

Wall-Mount Monitor Arm - Dual Swivel - For up to 34" (33.1lb/15kg) Displays

Product ID: ARMWALLDS



Wall-mount your computer monitor or flat-screen TV to free up space on your desk or table. This wall-mount monitor arm supports flat-panel displays up to 34" and provides a full 15" (382 mm) arm extension for optimum screen adjustment. The pivoting arm swivels +90 / - 90, plus tilts and rotates to provide maximum viewing flexibility.

This monitor arm helps you save space on your desk or table surface, by letting you securely wall-mount a computer monitor or TV from 13" to 34" in size and up to 33 lb. (15kg) in weight. It's ideal for many different applications, including business, healthcare or financial settings, where you may want to share your screen with patients, clients, or other visitors. The wall-mount monitor arm also works well in office settings or workspaces that back against a wall.

The monitor arm extends a full 15" (381 mm) making it easy to change your screen position, so you can work more comfortably or share your screen with others. The dual-swivel arm offers a full +90 / - 90 swivel, to move your screen easily to the left or right and share your screen with maximum viewing flexibility. It tilts freely +70 / - 70, allowing easy angle adjustment up or down to share your display, while collaborating with team members.

The aluminum wall-mount monitor arm features slide-in wall plate construction for easy installation. To help keep your work area free of clutter, the monitor arm also features a cable clip that keep your cables neatly out of sight.

The ARMWALLDS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Free up desk or table space in business, commercial, industrial or office settings

- Share your monitor with clients, for easy collaboration in office settings such as healthcare, financial or real estate
- Create space in home office settings

Features

- Wall mount a VESA (75x75, 100x100) compatible display 13" to 34", flat screen, curved or ultrawide, with a max weight of 33.2 lb. (15 kg)
- Save space by wall mounting your monitor or flat-screen TV and easily share your screen
- Arm extends a full 15" (382 mm)
- Pivoting arm with +90 / - 90 swivel to provide maximum viewing flexibility
- Tilts freely +70 / - 70, allowing easy angle adjustment up or down
- Easy installation with slide-in wall plate construction
- Supports VESA mount compliant monitors: 75x75, 100x100
- Cable management

Hardware

Warranty	5 Years
Cable Management	Yes
Articulating	No
# of Displays Supported	1
Mounting Options	Wall-Mount
VESA Hole Pattern(s)	75x75 mm 100x100 mm

Performance

Weight Capacity (Per Display)	33.1 lb [15 kg]
Minimum Display Size	13"
Maximum Display Size	34"
Fits Curved Display	Yes

Height Adjustment	No
Maximum Arm Extension	15.0 in [382 mm]
Display Tilt	+70 / - 70
Swivel / Pivot	+90 / - 90
Display Rotation	0

Physical Characteristics

Color	Black
Material	Aluminum
Product Length	15.7 in [40 cm]
Product Width	4.7 in [12 cm]
Product Height	4.7 in [12 cm]
Weight of Product	33.5 oz [948 g]

Packaging Information

Package Quantity	1
Package Length	6.5 in [16.4 cm]
Package Width	9.3 in [23.7 cm]
Package Height	2.4 in [60 mm]
Shipping (Package) Weight	2.4 lb [1.1 kg]

What's in the Box

Included in Package	1 - display arm
	1 - mounting plate
	1 - 2.5 mm hex key
	1 - 4 mm hex key
	1 - 5 mm hex key
	1 - set screw

4 - M4x14 mm screws

4 - M5x14 mm screws

2 - screws

2 - wall screws

1 - instruction manual

****Product appearance and specifications are subject to change without notice.***