

USB-C Cable with Power Delivery (3A) - M/M - 2 m (6 ft.) - USB 3.0 (5Gbps) - USB-IF Certified

Product ID: USB315CC2M



This USB 3.2 Gen 1 USB-C cable lets you connect your USB Type-C devices for syncing, charging and powering your devices. USB 3.2 Gen 1 is also known as USB 3.0 (5Gbps).

The cable is also compatible with Thunderbolt 3 ports, which means you can charge and sync your USB-C mobile devices using your Thunderbolt 3 laptop.

With up to 3A (60W) of power output, you can use this USB Type-C cable to power your USB-C hard drive from the USB-C port on your laptop.

You can also power a USB-C laptop, such as your Apple MacBook or Chromebook Pixel. Simply connect the cable to your USB-C laptop and to a USB-C wall charger.

With 3A of power delivery, you will be able to charge your mobile devices faster than with a regular USB-C 3.0 cable.

The 2-meter cable gives you the extra length you need to overcome distance restrictions and stay connected. You can charge and sync your USB-C mobile device in almost any environment. Even while you're taking notes in a boardroom, catching up on emails in your hotel room, or reading in a coffee shop, your mobile device will reach your computer or wall charger more comfortably.

The cable supports full 4K 60Hz video and DisplayPort 1.2 and is compatible with existing DisplayPort displays. It's ideal for connecting your docking station or laptop to a monitor with astonishing resolution, contrast, and color depth for amazing detail.

The cable has undergone rigorous compliance testing and is certified by USB-IF (USB Implementers Forum) to meet all USB 3.2 Gen 1 specifications. This includes all environmental, electrical and mechanical standards, which ensures a reliable, high-quality cable for all of your USB-C devices.

The USB315CC2M from StarTech.com is backed by a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power your USB-C hard drive from your USB-C laptop
- Power your USB-C laptop from a USB Type-C wall charger
- Fast charge your USB-C mobile devices from your USB-C laptop or wall charger
- Sync your USB-C mobile devices with your USB-C computer

Features

- USB-IF Certified
- Provides up to 3 amps of power output for fast charging your mobile devices, or powering your USB-C peripheral devices or laptop
- Supports data transfer rates up to 5Gbps (USB 3.2 Gen 1)
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K @ 60Hz
Type and Rate	USB 3.0 - 5 Gbit/s

Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
-------------	---

Connector B	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
-------------	---

Power

Power Delivery	60W
----------------	-----

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	26 AWG (0.404 mm)
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.5 in [1.2 cm]
Product Height	0.3 in [6.4 mm]
Weight of Product	3.2 oz [92.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.6 in [1.6 cm]
Shipping (Package) Weight	3.6 oz [102.0 g]

What's in the Box

Included in Package	1 - USB-C cable
---------------------	-----------------

**Product appearance and specifications are subject to change without notice.*