HDMI Plug to VGA Receptacle Adapter

multicomp PRO

: HDMI Plug, 19 Pin

: 190mm

Operation Temperature : -5°C to +40°C

: Black, White

: -25°C to +60°C

: VGA Receptacle, 15 Pin

: 10% to 85% (no condensation)

: 5% to 95% (no condensation)

RoHS

Compliant




Electronic Tests

Open / Short / Intermittence			
Hi-Pot			
Insulation Resistance			
Conductive Resistance			
Computer Test			

- : 100% : AC 300V, 0.01S, 1mA : DC 300V, 0.01S, 10MΩ Min. : 3Ω Max.
- : 1080P @ 60Hz

Diagram



Specifications

Storage Temperature

Operation Humidity

Storage Humidity

Convert From

Cable Length

Convert To

Colour

No.	Parameter	Specifications
1	Cable	UL20276 [32AWG(7/0.08TC) * 1P + D(7/0.08TC) + Al-My] * 5 + 32AWG(7/0.08TC) * 4C + D(7/0.08BC) + Al-Foil + B(80/0.12 Al-Mg), PVC Jacket, OD: 4.8±0.2mm
2	Connector - A	HDMI Male, 19 Pin, Nickel Plated Shell, Gold Flash Contact
3	Connector - B	VGA Female, 15 Pin, Nickel Plated Shell, Gold Flash Contact, with IC
4	Inner Mold	LDPE
5	Outer Mold	45P PVC
6	Hood	VGA Female: ABS
7	Dust Cover	HDMI Male: Transparent

Part Number Table

Description	Part Number
HDMI Plug to VGA Receptacle Adapter, 190mm, Black	PS000255
HDMI Plug to VGA Receptacle Adapter, 190mm, White	PS000256

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

