TECHNICAL PRODUCT DATASHEET

P3 PROTECTION

DISPOSABLE PROTECTION

ADDITIONAL IMAGES

UPDATED: 27/11/2020

UCFD-P3V

Itimate

Industria

FFP3 NR Fold Flat Mask With Valve.

Universally popular vertical fold flat FFP3 disposable respirator. Packed individually for easy hygienic dispensing.

Space saving design allows the mask to be stored whilst not in use. Integrated exhalation valve reduces breathing resistance and heat build up for superior user comfort.

Light and comfortable with a soft foam nose seal and adjustable nose clip that moulds to the users face to improve face fit percentage and enhance compatability with eyewear and reduced fogging. Colour coded nose clip, valve and strap for easy identification in the workplace. Maintenance free.



FEATURES AND TECHNOLOGY

REDUCED



BAGGED









TECHNICAL INFORMATION

ORDER REF #	RE/UC/UCFD-P3V	
VALVED	YES	
PACKING	PER BOX: 10 PCS	PER CASE: 20
SIZE	ONE SIZE	
EU TYPE CERTIFICATION AND ONGOING CONFORMITY PERFORMED BY	INSPEC International B.V. Beechavenue 54-62, 1119 PW, SchipholRijk, Netherlands (Notified Body No. 2849)	



F)



📵 Phone: +44 (0)1902 451 451

🔲 Fax: +44 (0)1902 451 271

Email: sales@ultimateindustrial.co.uk

Web: www.ultimateindustrial.co.uk

© 2020. Ultimate Cleaners (Industrial) Ltd. Victoria House, Colliery Road, Wolverhampton, WVI 2RD, UK. Registered in England No. 2035621

Ultimate

Industrial

Leadership in

PROTECTION.™

TECHNICAL PRODUCT DATASHEET

P3 PROTECTION

DISPOSABLE PROTECTION

UPDATED: 27/11/2020

COLOUR CODED LEGEND:

All our masks are colour coded for easy identification of protection levels		
PI PROTECTION	P2 PROTECTION	P3 PROTECTION
Masks are identifiable by yellow markings and suitable for use with fine dusts, fumes, water and oil based mists/ aerosols.	Masks are identifiable by blue markings and suitable for use with fine toxic dusts, fumes, water and oil based mists/	Masks are identifiable by red markings and suitable for use as P2, but at higher concentration levels and welding.

FURTHER INFORMATION

STORAGE / TRANSPORT: Keep away from direct sunlight; store in a cool dry place. Keep away from ozone sources or naked flame. Store in their original packaging. Store between 0°C and 40°C.

PRECAUTIONS BEFORE USE: A properly selected respirator is essential to protect your health. Before using this respirator consult a suitably qualified Safety Professional to determine the suitability of the product for your intended use.

OBSOLESCENCE: When stored as recommended, these masks will not suffer a change in mechanical properties for to up 4 years from date of manufacture shown. Once this date has been reached, this product should be withdrawn from use.

TRANSPORTATION: During transportation, ensure the product is well packaged to prevent damage that may impair the masks efficiency.

CAUTIONS AND LIMITATIONS:

1. Not for use in atmospheres with less than 19.5% oxygen. 2. Do not use in atmospheres immediately dangerous to life or health.
3. Do not exceed maximum use concentrations established by regulatory standards 4. Failure to properly use and maintain this product could result in injury or death 5. All approved respirators should be selected, fitted, used and maintained in accordance with MSHA, OSHA and other applicable regulations. 6. Never substitute, modify, add or omit parts in the configuration as specified by the manufacturer. 7. See information on this packaging for use and maintenance of these respirators. 8. NIOSH does not evaluate respirators as surgical masks. 9. Fit according to supplied instructions.

WARNING: READ THE ACCOMPANYING INSTRUCTIONS FULLY BEFORE USING THIS PRODUCT. FAILURE TO FOLLOW THE INSTRUCTIONS AND LIMITATIONS ON THE USE OF THIS PRODUCT COULD REDUCE THE EFFICIENCY OF THE RESPIRATOR AND RESULT IN SERIOUS DAMAGE TO HEALTH OR DEATH.

For more information about this product, or to access the Declaration of Conformity or Product Certification, visit; https://www.ultimateindustrial.co.uk/product/473-UCFD-P3V

If appropriate to the product, EC/EU Declaration of Conformities, relevant certification and supporting documentation are available to access through your distributor, at the above web address(s) or by contacting UCi customer services quoting the product reference code. This document and any other statement provided herein by or on behalf of UCi are given for informational purposes and do not constitute a contractual agreement nor warranty of merchantability. UCi assumes no responsibility for the suitability or adequacy of an end user's selection of product for a specific purpose. The manufacturer reserves the right to make any modifications it deems necessary. All product and company names are trademarks[™] or registered[®] trademarks of their respective holders. © UCi Limited, 2020



Phone: +44 (0)1902 451 451

Fax: +44 (0)1902 451 271

Email: sales@ultimateindustrial.co.uk

🔊 Web: www.ultimateindustrial.co.uk



Leadership in PROTECTION.™

© 2020. Ultimate Cleaners (Industrial) Ltd. Victoria House, Colliery Road, Wolverhampton, WV1 2RD, UK. Registered in England No. 2035621