



Part Number : [330122003](#)
Product Description : MX150 Female Terminal
for Mat-Sealed Connectors, Tin Plating, 22
AWG, Right Reel Payoff
Series Number : 33012
Status : Active
Product Category : Crimp Terminals



Documents & Resources

Drawings

[Drawing 330122003_sd.pdf](#)
[Packaging Design Drawing 313025040-000.pdf](#)

Specifications

[Application Specification 330120000-AS-KR-000.pdf](#)
[Test Summary TS-33012-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 34; 44; 33
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	33012
Description	MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 22 AWG, Right Reel Payoff
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.
Product Family	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	822350084246

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Physical

Gender	Female
Grip Code	22
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.391/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression

Wire Insulation Diameter	1.70mm max.
Wire Size (AWG)	22
Wire Size mm ²	0.50

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
MX150 Mat-Sealed Single Row Female Connector Assemblies	<u>33471</u>
MX150 Mat-Sealed Dual Row Female Connector Assemblies	<u>33472</u>

Application Tooling

Global

Description	Part Number
Extraction Toolkit for MX150 Connectors	<u>2002220700</u>
PremiumGrade Hand Crimp Tool for MX150 Female Terminals, 18-22 AWG	<u>0638116000</u>
Hand Crimp Tool Metric 0.5 and 0.75	<u>0638116200</u>
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	<u>0638131500</u>
ServiceGrade Hand Crimp Tool for MX150 Crimp Terminals, 14-22 AWG	<u>0640160133</u>