

GEARWRENCH FORGE AHEAD




Storage Products



GEARWRENCH GSX Tool Storage products are built for the day-to-day needs of professional users. Designed with durability, access and maximum storage capacity in mind, they provide superior tool storage solutions for the toughest work environments. GSX tool chests, cabinets, and tool carts are designed to optimize even the most advanced user's workspace and include features like a textured coated finish, integrated power strips, heavy-duty industrial casters, and aluminum drawer pulls. When paired with our full line of mechanics hand tools, GEARWRENCH GSX Tool Storage products cover the needs of every level of a professional user.

Tool Cabinets



Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity
83248	72" 18 Drawer GSX Series Rolling Tool Cabinet with Stainless Steel Worktop (Black Drawer Pull)	72.625"	24"	47"	751 lbs.	36107.9 in ³
83249	72" 18 Drawer GSX Series Rolling Tool Cabinet with Stainless Steel Worktop (Chrome Drawer Pull)	72.625"	24"	47"	751 lbs.	36107.9 in ³

83248 & 83249 - 72" 18 Drawer Cabinet

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top 1	49.6"	21.4"	5.2"	300 lbs
Top 2	49.6"	21.4"	2.6"	150 lbs
Top Left	15.1"	21.4"	2.6"	150 lbs
Middle Left 1	15.1"	21.4"	2.6"	150 lbs
Middle Left 2	15.1"	21.4"	4.6"	300 lbs
Bottom Left	15.1"	21.4"	9.8"	300 lbs
Top Middle	31.7"	21.4"	2.6"	150 lbs
Middle Middle 1	31.7"	21.4"	2.6"	150 lbs
Middle Middle 2	31.7"	21.4"	4.6"	300 lbs
Middle Middle 3	31.7"	21.4"	4.6"	300 lbs
Bottom Middle	31.7"	21.4"	4.6"	300 lbs
Top Right	15.1"	21.4"	5.2"	300 lbs
Middle Right 1	15.1"	21.4"	2.6"	150 lbs
Middle Right 2	15.1"	21.4"	2.6"	150 lbs
Middle Right 3	15.1"	21.4"	2.6"	150 lbs
Middle Right 4	15.1"	21.4"	4.6"	300 lbs
Middle Right 5	15.1"	21.4"	4.6"	300 lbs
Bottom Right	15.1"	21.4"	4.6"	300 lbs

Tool Cabinets



Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity
83247	52" 11 Drawer GSX Series Rolling Tool Cabinet with Stainless Steel Worktop	52"	18"	36"	326 lbs.	17367.0 in ³

83247 - 52" 11 Drawer Cabinet

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top	47.6"	15"	4.8"	200 lbs
Top Left	31.6"	15"	2.9"	100 lbs
Middle Left 1	31.6"	15"	2.9"	100 lbs
Middle Left 2	31.6"	15"	2.9"	100 lbs
Middle Left 3	31.6"	15"	2.9"	100 lbs
Middle Left 4	31.6"	15"	2.9"	100 lbs
Bottom Left	31.6"	15"	6"	200 lbs
Top Right	13.6"	15"	2.9"	100 lbs
Middle Right 1	13.6"	15"	2.9"	100 lbs
Middle Right 2	13.6"	15"	2.9"	100 lbs
Bottom Right	13.6"	15"	12"	200 lbs

Tool Cabinets



83245
41" Cabinet



83243
36" Cabinet



83241
26" Cabinet

Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity
83245	41" 11 Drawer Tool Cabinet	41.1"	18.2"	41.4"	208.3 lbs	13636.33 in ³
83243	36" 6 Drawer Tool Cabinet	36.2"	18.2"	38.6"	158.8 lbs	13057.24 in ³
83241	26" 5 Drawer Tool Cabinet	26.7"	18.2"	37.2"	118.4 lbs	8586 in ³

83245 - 41" 11 Drawer Cabinet

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top	36.8"	15"	4.8"	100 lbs
Top Left	20.7"	15"	3"	100 lbs
Middle Left 1	20.7"	15"	3"	100 lbs
Middle Left 2	20.7"	15"	3"	100 lbs
Middle Left 3	20.7"	15"	6.1"	100 lbs
Bottom Left	20.7"	15"	9.2"	200 lbs
Top Right	13.7"	15"	3"	100 lbs
Middle Right 1	13.7"	15"	3"	100 lbs
Middle Right 2	13.7"	15"	3"	100 lbs
Middle Right 3	13.7"	15"	6.1"	100 lbs
Bottom Right	13.7"	15"	9.2"	200 lbs

83243 - 36" 6 Drawer Cabinet

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top Left	31.9"	15"	3"	100 lbs
Middle 1	31.9"	15"	3"	100 lbs
Middle 2	31.9"	15"	3"	100 lbs
Middle 3	31.9"	15"	3"	100 lbs
Middle 4	31.9"	15"	6.1"	200 lbs
Bottom	31.9"	15"	9.2"	200 lbs

83241 - 26" 5 Drawer Cabinet

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top	23.1"	15"	2.5"	100 lbs
Middle 1	23.1"	15"	3.3"	100 lbs
Middle 2	23.1"	15"	3.3"	100 lbs
Middle 3	23.1"	15"	6.1"	100 lbs
Bottom	23.1"	15"	9.7"	100 lbs

Tool Chests



83244
41" Chest



83242
36" Chest



83240
26" Chest

Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity	Till Width	Till Depth	Till Height	Power Strip
83244	41" 5 Drawer Tool Chest	40.6"	17.8"	23"	127.2 lbs	11376.3 in ³	38"	17.7"	10.4"	Yes
83242	36" 5 Drawer Tool Chest	35.7"	17.8"	23"	115.8 lbs	10067.1 in ³	33.2"	17.7"	10.4"	Yes
83240	26" 4 Drawer Tool Chest	26"	16"	20.7"	81 lbs	5117 in ³	23.9"	16.6"	3.7"	No

83244 - 41" 5 Drawer Chest

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top Left	20.7"	15"	3"	100 lbs
Middle Left	20.7"	15"	3"	100 lbs
Top Right	13.7"	15"	3"	100 lbs
Middle Right	12.7"	15"	3"	100 lbs
Bottom	36.8"	15"	6.1"	100 lbs

83242 - 36" 5 Drawer Chest

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top Left	14.7"	15"	3"	100 lbs
Middle Left	14.7"	15"	3"	100 lbs
Bottom Left	14.7"	15"	3"	100 lbs
Top Right	14.7"	15"	3"	100 lbs
Bottom Right	14.7"	15"	6.1"	200 lbs

83240 - 26" 4 Drawer Chest

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top	22.8"	13.8"	2"	100 lbs
Middle 1	22.8"	14.1"	3.3"	100 lbs
Middle 2	22.8"	14.1"	3.8"	100 lbs
Bottom	22.8"	14.1"	3.8"	100 lbs

Tool Chest & Cabinet Combinations

20 Gauge Steel Cabinet and Chest

For strength and durability

Gas Charged Lift Support Struts

Supports easy lid opening and closing

Black Foam Mat Liner Included

For each drawer and top storage space for chests and cabinets

Tubular Barrel Lock and Key

For added security and protection

22 Gauge Steel Drawers

For strength and durability

Heavy Duty Industrial Polyurethane Casters

2 Fixed and 2 swivel, providing easy mobility. Each caster weight rated at 450 lbs.



Power Strip Mounted Inside Lid
With 4 outlets, 2 USB ports, and on/off switch

Trigger Lock System Drawer Release

Allows drawers to naturally open and close

Ball Bearing Slides

Offer exceptional load capacity and easy slide action

Auto Return Sliding Drawer System

For added protection of drawer contents

Textured Coated Paint Finish

Offers increased resistance to corrosion, weather, and staining

83244 & 83245
41" Chest and Cabinet

Tool Chest & Cabinet Combinations



26" Chest and
Cabinet Combination



36" Chest and
Cabinet Combination



41" Chest and
Cabinet Combination

	26" Chest and Cabinet Combination	36" Chest and Cabinet Combination	41" Chest and Cabinet Combination
Tool Chest	83240 26" 4 Drawer Tool Chest	83242 36" 5 Drawer Tool Chest	83244 41" 5 Drawer Tool Chest
Tool Cabinet	83241 26" 5 Drawer Tool Cabinet	83243 36" 6 Drawer Tool Cabinet	83245 41" 11 Drawer Tool Cabinet
Total Storage Capacity	13703 in ³	23124.34 in ³	25012.63 in ³

Tool Carts



Customizable Partitions
In top drawer for ease-of-use

Deeper Drawers
For 20% greater storage

Ball Bearing Slides
Offer exceptional load capacity and easy slide action



Pegboard Surface and Can Shelf
On opposite side of locking cabinet

Vise Mount Capability
For heavy-duty work

Integrated Charging Station
With 6 outlets and 2 USB ports

Heavy-Duty 20 Gauge Steel
For superior frame and drawer strenght

Secure Lockable Side Cabinet
Is separate from the drawers

83169
Mobile Work Station

Extra-Large 6" x 2" Polyurethane Casters
2 stationary and 2 dual-locking that lock caster pivot and wheel rotation

Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity
83169	Mobile Work Station	42.5"	25.4"	41"	317 lbs	18895 in ³

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top	36.8"	15"	4.8"	100 lbs
Top Left	20.7"	15"	3"	100 lbs
Middle Left 1	20.7"	15"	3"	100 lbs
Middle Left 2	20.7"	15"	3"	100 lbs
Middle Left 3	20.7"	15"	6.1"	100 lbs
Bottom Left	20.7"	15"	9.2"	200 lbs
Top Right	13.7"	15"	3"	100 lbs
Middle Right 1	13.7"	15"	3"	100 lbs
Middle Right 2	13.7"	15"	3"	100 lbs
Middle Right 3	13.7"	15"	6.1"	100 lbs
Bottom Right	13.7"	15"	9.2"	200 lbs

Tool Carts

Tubular Barrel Lock and Key
For added security and protection

Gas Charged Lift Support Struts
Supports easy lid opening and closing

Power Strip Mounted Inside Lid
With 4 outlets, 2 USB ports, and on/off switch

Built-In Side Screwdriver Storage
For easy access to screwdriver handle items



Coated Finish Inner Arc Side Handle
Provides resistance protection and ease to move cart

Aluminum Drawer Pulls
Supports easier drawer opening

Textured Coated Paint Finish
Offers increased resistance to corrosion, weather, and staining

Heavy Duty Industrial Polyurethane Casters
2 Fixed and 2 swivel, providing easy mobility. Each caster weight rated at 450 lbs.

83246
35" 7 Drawer Tool Cart

Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity
83246	35" 7 Drawer Tool Cart with Lift Top	35"	20"	39"	213 lbs	16244.6 in ³

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Top	30"	18"	2.9"	100 lbs
Middle 1	30"	18"	2.9"	100 lbs
Middle 2	30"	18"	2.9"	100 lbs
Middle 3	30"	18"	2.9"	100 lbs
Middle 4	30"	18"	2.9"	100 lbs
Middle 5	30"	18"	2.9"	100 lbs
Bottom	30"	18"	6.1"	200 lbs



Recessed 'Through Holes' In Till Area
Allow for the secure storage of extra long items like pry bars

Heavy-Duty Chrome Side Handle
With rubber grip for durability and control

Heavy Gauge Steel Body
For 650 lb. load capacity

Smooth Bottom Tray and Durable Side Storage
Ideal to hold a range of items

Full-Height Corner Bumpers
Protect cart and surroundings


Heavy-Duty Polyurethane Casters
2 stationary and 2 dual-locking that lock caster pivot and wheel rotation

83168
33" 4 Drawer Tool Cart

Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity
83168	33" 4 Drawer Tool Cart	33"	21.1"	41.7"	153.3 lbs	650 lbs

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Till	31.7"	18.5"	4.9"	100 lbs
Top Left	13.2"	17.4"	2.7"	100 lbs
Top Right	13.2"	17.4"	2.7"	100 lbs
Middle 1	27.5"	17.4"	2.7"	100 lbs
Bottom Drawer	27.5"	17.4"	6.7"	100 lbs
Bottom Tray	32.1"	20.2"	3.2"	100 lbs

Tool Carts



Recessed 'Through Holes' In Till Area
Allow for the secure storage of extra long items like pry bars

External Power Tool Rack
Provides easy access

Smooth Bottom Tray
Ideal for storage

Corner Bumpers
Minimize damage to cart or surroundings

Heavy-Duty Polyurethane Casters
2 stationary and 2 dual-locking that lock caster pivot and wheel rotation

83167
32" 2 Drawer Tool Cart

Cat. No.	Description	Overall Width	Overall Depth	Overall Height	Overall Weight	Total Storage Capacity
83167	32" 2 Drawer Tool Cart	32.5"	20.5"	41"	110.5 lbs	450 lbs

Drawer Description	Drawer Width	Drawer Depth	Drawer Height	Drawer Load Weight
Till	31.7"	18.5"	4.9"	100 lbs
Top Drawer	27.5"	17.4"	2.7"	100 lbs
Bottom Drawer	27.5"	17.4"	2.7"	100 lbs
Bottom Tray	32.1"	20.2"	3.2"	100 lbs

Warranty Information



83249



83248



83247



83245



83243



83241



83244



83242



83240



83169



83246



83168



83167

Cat. No.	Description	Warranty
83249	72" 18 Drawer Tool Cabinet With Chrome Drawer Pulls	3 Years Limited Warranty
83248	72" 18 Drawer Tool Cabinet With Black Drawer Pulls	3 Years Limited Warranty
83247	52" 11 Drawer Tool Cabinet	3 Years Limited Warranty
83245	41" 11 Drawer Tool Cabinet	3 Years Limited Warranty
83243	36" 6 Drawer Tool Cabinet	3 Years Limited Warranty

Cat. No.	Description	Warranty
83241	26" 5 Drawer Tool Cabinet	3 Years Limited Warranty
83244	41" 5 Drawer Tool Chest	3 Years Limited Warranty
83242	36" 5 Drawer Tool Chest	3 Years Limited Warranty
83240	26" 4 Drawer Tool Chest	3 Years Limited Warranty
83169	Mobile Work Station	5 Years Limited Warranty

Cat. No.	Description	Warranty
83246	35" 7 Drawer Tool Cart With Lift Top	3 Years Limited Warranty
83168	33" 4 Drawer Tool Cart	5 Years Limited Warranty
83167	32" 2 Drawer Tool Cart	5 Years Limited Warranty

