


Fine Wire Disc Thermocouple, PFA with Bare Tails or Miniature Plug - JIS



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description	Exposed junction thermocouple with Copper Disc brazed at tip		
Sensor Type	Copper disc, 6.35mm diameter x 0.3mm thick		
Thermocouple Type	Type K		
Thermocouple Junction	Grounded measuring junction		
Cable Length	1m, 2m, 5m		
Cable Type	1/0.2mm PFA Teflon® insulated twisted wire		
Termination Type	Miniature Plug or Bare tails		
Max. Temperature	200°C		
Min. Temperature	0°C		
Standards Met	JIS (Japanese Industrial Standards)		
Colour	Positive: Red / Negative: White		
Accessories	Supplied with high temperature adhesive kapton strips (13x18mm x 5) for quick and easy attachment to surface/process		

Ordering Information

Туре	Cable Length	Termination	Manufacturers Code	Farnell Order Code
K	1m	Miniature Plug	Z2-K-1-MP-DISC-JIS	4156003
K	2m	Miniature Plug	Z2-K-2-MP-DISC-JIS	4156004
K	5m	Miniature Plug	Z2-K-5-MP-DISC-JIS	4156005
K	1m	Bare Tails	Z2-K-1-T-DISC-JIS	4156007
K	2m	Bare Tails	Z2-K-2-T-DISC-JIS	4156008
K	5m	Bare Tails	Z2-K-5-T-DISC-JIS	4156009

TC-21 Nov-23



Thermocouple & PRT Cable

Thermocouple cables are available in IEC or ANSI colour codes. Insulation types include PFA, PTFE, PVC &

Fibreglass. Available spool lengths include 10, 25, 50, 100 and 200m.

Best Sellers



ANSI PTFE Insulated Twin Twisted Farnell 2443696 Newark 73AC8304

ANSI PFA Insulated Twin Twisted Farnell 2443711 Newark 73AC8297

Fabricated and Specialist Thermocouples

Styles include; Magnet, Washer, Nozzle, Leaf, Bayonet & Bolt thermocouple. Various lengths and calibration types available.

Best Sellers




Washer Thermocouple Farnell 8597952 Newark 38K1555



Bayonet Thermocouple Farnell 2785115 Newark 37AC0993

Magnet Thermocouple Farnell 2081298 Newark 88T2877



Including exposed junctions with fitted or moulded miniature plug and insulated leads, ideal for test and development applications.

1, 2, 3, 5 & 10m lengths available in IEC or ANSI colours.

Best Sellers



IEC Type T Exposed Junction Farnell 7076186 Newark 68C2613

IEC Type K Exposed Junction Farnell 4100748 Newark 15J1022



Thermocouple Connectors

Range of miniature or standard thermocouple connectors. Available in thermocouple types K, J, T, E, N, RS, B, and copper. IEC, ANSI & JIS colour codes available.



IEC Thermocouple PCB Socket Farnell 2347056 **Newark 06X5514**



IEC Thermocouple Plug

Farnell 7086362 **Newark 67C1559**



ANSI Thermocouple Socket

> Farnell 2347121 Newark 06X4819



RTD Detectors

Wire-wound type provides greater accuracy and stability but are vulnerable to shock.

Flat film type are resistant to shock and have quicker thermal response times.

Various lengths and diameters available, in class A, B and 1/10th Din.

Best Sellers



Farnell 8598550 Newark 38K0883

PT100 Wire **Wound Detector**

Farnell 2770776 Newark 25AC2608

PT100 Class A Thin Film Detector

Farnell 8598525 **Newark 38K0885**



Mineral Insulated Thermocouples

Available in various calibration types with a variety of terminations.

These include; Thermocouple plugs, Terminal heads and Thermocouple cable.





ANSI Thermocouple Farnell 2420317 Newark 53X3217

IEC Thermocouple with Mini Plug Farnell 4248338

Newark 19J1166

IEC Melt Bolt Thermocouple Farnell 2816490 Newark 44AC8638



Best Sellers



Pt100 Heavy Duty Sensor Probe Farnell 8598096 Newark 38K0974



Pt100 Sensor in Stainless Steel Tube with Teflon Lead Farnell 2420300 Newark 53X3459

Pt100 Outdoor/ Cold Store Temperature Sensor

Farnell 2816462 Newark 44AC8648

L60 Fine Wire Thermocouple Welder

The Thermocouple Welder is a compact, simple-to-use instrument designed for thermocouple and fine wire welding. Supplied with foot switch, spare electrodes, pliers & safety glasses, impact clip and pen plate.

Best Sellers





L60+ Thermocouple & Fine Wire Welder and accessories Farnell 2897470 Newark 62AC8741

To suit a wide range of applications and styles, available in class A or B.

Resistance Thermometer

Detectors (RTD) / Platinum

Resistance Thermometers (PRT)

TC-21

Nov-23