

3M[™] E-A-R[™] Classic[™] Earplugs

Key benefits:



Comfortable

- Industry first foam with slow recovery time helps achieve secure and comfortable fit
- Soft foam helps provide low pressure inside the ear canal thus increasing comfort and wearability




Convenient

- Available in both corded and uncorded versions
- Compatible with
 3M[™] One Touch[™] Pro Dispenser



Protective

- Fits most ear canals and provides a reliable seal
- Exposed cell surface resists movement and helps maintain an effective seal
- Sweat and humidity resistant for an effective seal over long shifts
- Compatible with 3M™ E-A-RFit™ Dual Ear Validation System which measures the effectiveness of the earplug's protection level



94dB-105dB (A)







3M™ E-A-R™ Classic™

Suggested for noise levels within this range.

Materials

The following materials are used in the manufacture of this product:

Component	Material				
Earplugs	Proprietary slow recovery polymer foam				
Cord	Recycled polymer				

Attenuation values

Frequency (Hz)	63	125	250	500	1000	2000	4000	8000
Corded								
Mf (dB)	21.7	23.7	26.1	30.4	30.1	33.8	42.6	42.1
sf (dB)	6.3	5.6	5.2	5.7	5.3	4.6	4.0	5.7
APVf (dB)	15.4	18.0	20.9	24.6	24.9	29.2	38.6	36.4
Uncorded								
Mf (dB)	22.3	23.3	24.6	26.9	27.4	34.1	41.6	40.4
sf (dB)	5.4	5.3	3.6	5.4	4.8	3.1	3.5	6.4
APVf (dB)	16.9	18.1	20.9	21.5	22.6	30.9	38.1	34.0
O I I CNID OO ID		ID 14 C	00 10 1	00 ID				

Corded: SNR = 29dB. H = 30dB. M = 26dB. L = 23dB. Unorded: SNR = 28dB. H = 30dB. M = 24dB. L = 22dB.

Key

APVf (dB) = Mf -sf (dB)

Mf = Mean
attenuation value

sf = Standard deviation

APVf = Assumed protection value

H = High-frequency attenuation value

M = Medium-frequency attenuation value

L = Low-frequency attenuation value

SNR = Single number rating (the value that is subtracted from the measured C-weighted sound pressure level, L(C) in order to estimate the effective A-weighted sound pressure level inside the ear)

Ordering information

Short ID	Description			
3M™ E-A-R™ Classic™				
PP01002	3M™ Classic™ Earplugs pillowpack			
CC01000	3M™ Classic™ Earplugs corded			
3M [™] E-A-R [™] One Touch Pro Dispenser				
391-0000	E-A-R One Touch pro earplug dispenser (dispenser only)			
PD01001	1 3M™ Classic™ Earplugs refill bottle			
3M [™] E-A-RFit [™] Dual Ear Validation System				
393-1100	E-A-RFit Dual Ear Validation System			
CLASSICP	3M™ Classic™ Earplugs probed test plugs			

Personal Safety Division

3M United Kingdom PLC 3M Centre, Cain Road, Bracknell Berkshire RG12 8HT t: 0870 60 800 60 www.3M.co.uk/safety

3M Ireland Limited The Iveagh Building The Park Carrickmines Dublin 18