

Part Number : 08701039 Product Description : 2.50mm Pitch, Mini-SPOX Female Crimp Terminal, 22-28 AWG, Reel Series Number : 5263 Status : Active Product Category : Crimp Terminals Engineering Number : 5263PBT Packaging Alternative : 0008701040 (Bag)



### **Documents & Resources**

Drawings Drawing 008701039\_sd.pdf

### 3D Models and Design Files

3D Model 008701039\_stp.zip

### Specifications

Packaging Specification 52639200-SPK-200.pdf Product Specification 52641001-PS-000.pdf Product Specification PS-5264-001-001.pdf

### **Tooling Specifications**

Crimp Specification CS-5263-001.pdf

## Product Environment Compliance

#### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	©
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

# Part Details

### General

Status	Active
Category	Crimp Terminals
Series	5263
Description	2.50mm Pitch, Mini-SPOX Female Crimp Terminal, 22-28 AWG, Reel
Application	Signal, Wire-to-Board
Product Family	Mini-SPOX Wire-to-Board Connector System
Product Name	Mini-SPOX
UPC	800753534902

#### Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	43.200/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size (AWG)	22, 24, 26, 28

Wire Size m	וm²
-------------	-----

# Use with Part(s)

Description	Part Number
Mini-SPOX Single Row Receptacle Housings	<u>5264</u>

## Application Tooling

### Global

Description	Part Number
Extraction Tool for SPOX, MX64, Ditto, MX150CE, Milli-Grid Terminals	<u>0638131400</u>
Hand Crimp Tool for 2.50mm Pitch SPOX Crimp Terminal, 22-28 AWG	0638281900
FineAdjust Applicator for 2.50mm Pitch Crimp Terminal	0639023100
FineAdjust Applicator for 2.50mm (.098") Pitch SPOX Crimp Terminal	0639026400
T2 Terminator for 2.50mm Pitch Crimp Terminal	0639123100

# Application Tooling

Japan

Description	Part Number
S-1 Applicator for SPOX Female Terminals, 22-28 AWG	2023523700

This document was generated on Dec 16, 2023