

8-Port PCI Express RS232 Serial Adapter Card - PCIe RS232 Serial Card - 16C1050 UART -Multiport Serial DB9 Controller/Expansion Card - 15kV ESD Protection - Windows & Linux

Product ID: PEX8S1050



Add eight RS-232 DB9 serial ports to your desktop computer, through a PCIe expansion card slots. This PCI express serial card, with 8-port breakout cable, provides you with multiple ports to connect a wide variety of serial peripherals, at speeds of up to 921.4Kbps.

The PCI express serial port card makes it easy to add serial ports to connect your peripherals including printers, scanners, credit/debit card readers, PIN pads and modems, industrial controls and more. The 8 port PCIe serial card includes a breakout cable - with 8 DB9 connectors.

With broad OS support, including for Windows and Linux, this PCI Express card is easy to integrate into mixed environments.

PEX8S1050 is backed by a StarTech.com lifetime warranty and free lifetime technical support.



Certifications, Reports and Compatibility

Applications

• Manufacturing (CNC machinery, process control equipment, bar code scanners, serial printers)



- POS (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- Consumer (modems, PDAs, digital cameras, printers)
- Security (UPS control, access key panels, video cameras, card readers, modems)
- Casino (video lottery terminals, slot machines)
- Environmental Control (lighting, temperature, clocks)
- Healthcare (patient monitoring equipment, nurses' stations, modems)
- Hotel Front Desk (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- Hospitality/Restaurant (credit card/debit card reader, serial printers)
- ISDN Networking

Features

• 8 PORT SERIAL CARD: Serial controller card w/ 16C1050 UART based on the Systembase SB16C1058PCI, w/15kV ESD, 8x DB9 ports, bi-directional RS232 speeds up to 921.6Kbps per port & 256 byte FIFO buffer; Upgraded version of our popular card PEX8S952

• OPTIONAL CONFIGURABLE POWER: Multiport serial card provides 12v/5v, or none on pin 9 w/up to 3A total shared; 18"/48cm DB62 to 8x DB9 breakout cable incl; Hex nuts incl for opt screw/nut DB9 interface

• COMPATABILITY: Full profile PCI-e 1x card and fully compliant w/ PCI Express Base Specifications, Revision 1.0a/1.1; Supports Windows (incl. XP and up) and Linux; For standard profile desktop/servers

• VERSATILE APPLICATIONS: PCI Express RS232 serial adapter card for within point of sale terminals, PLCs, control/automation in factories, scientific sensors, medical equipment, scanners, oscilloscope

• STARTECH.COM ADVANTAGE: IT professionals choice for over 30 years; PCIe RS232 Serial expansion card is backed for life by StarTech.com, incl. free 24/5 North America based multi-lingual tech support

Hardware			
	Warranty	Lifetime	
	Ports	8	
	Interface	Serial	
	Bus Type	PCI Express	
	Card Type	Standard Profile	
	Port Style	Dongle (Included)	





	Industry Standards	16C1050 UART
	Chipset ID	ASMedia - ASM1083
		System Base - SB16C1058PCI
Performance		
	Serial Protocol	RS-232
	ESD Protection	+/-15kV (Air)
		+/-8kV (Contact)
	Max Baud Rate	921.6 Kbps
	Data Bits	5, 6, 7, 8
	FIFO	TX: 1-255 Byte
		RX: 1-255 Byte
		<i>* Depending on mode and configurations</i>
	Flow Control	Software (XON/XOFF), Hardware (RTS/CTS), and Xoff Re-Transmit function
	Parity	None, Even, or Odd
	Stop Bits	1, 1.5, 2
	General Specifications	Power on Pin 9: 12V DC, 5V DC or None
	MTBF	160,013 hours
Connector(s)		
	Connector Type(s)	1 - PCI Express x1
	External Ports	8 - DB-9 (9 pin, D-Sub)
Software		
	OS Compatibility	Windows CE 5.0, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11
		Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022
Power		
	Input Voltage	12V DC

12V DC

Output Voltage

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-40C to 75C (-40F to 167F)
Humidity	5~95% RH
Color	Yellow
Material	Steel
Cable Length	18.9 in [48 cm]
Product Length	4.1 in [10.5 cm]
Product Width	0.6 in [1.6 cm]
Product Height	4.7 in [12.0 cm]
Weight of Product	2.6 oz [74.0 g]
Package Quantity	1
Package Length	11.6 in [29.4 cm]
Package Width	7.6 in [19.2 cm]
Package Height	2.8 in [7.0 cm]
Shipping (Package) Weight	1.5 lb [0.7 kg]
Included in Package	1 - PCIe Serial Card
	1 - 18 in [48 cm] DB62 to 8 Port DB9 Breakout Cable
	1 - Full Profile Bracket (Installed)
	1 - Quick Start Guide
	Humidity Color Material Cable Length Cable Length Product Length Product Width Product Height Weight of Product Package Quantity Package Length Package Height Shipping (Package) Weight



*Product appearance and specifications are subject to change without notice.