

## 75 PIECE 1/4" Sq. Dr. MM/AF COMBINED SOCKET SET

### CATALOGUE ENTRY

**5 B75AM**  
**75 PIECE 1/4" Sq. Dr. MM/AF COMBINED SOCKET SET**

*Expert Quality*, manufactured from chrome vanadium steel hardened, tempered, chrome plated and polished for corrosion protection. Packed in blow mould carrying case and display sleeve.

Contents:

- 12 "Draper *Expert* HI-TORQ" 6 point sockets size: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 12.0 and 13.0mm
- 9 "Draper *Expert* HI-TORQ" 6 point sockets size: 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16 and 1/2" AF
- 10 "Draper *Expert* HI-TORQ" 6 point deep sockets size: 4.0, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0 and 13.0mm
- 6 "Draper *Expert* HI-TORQ" 6 point deep sockets size: 3/16, 1/4, 5/16, 3/8, 7/16 and 1/2" AF
- reversible ratchet with "quick release" button
- 3 extension bars size: 50, 75 and 150mm
- sliding tee bar
- flexible extension bar 150mm
- spinner handle
- flexible handle
- bit holder 1/4" sq. drive x 1/4" hexagon
- 4 plain slot insert bits size: 3.0, 4.0, 5.5 and 6.5mm
- 3 "PZ TYPE" insert bits No.1, 2 and 3
- 3 cross slot insert bits: No.1, 2 and 3
- 5 hexagon insert bits size: 3, 4, 5, 6 and 7mm
- 3 hexagon insert bits size: 1/8, 3/16 and 1/4" AF
- 11 "Draper TX-STAR" insert bits: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30 and T40

Stock No.	Euro per set	GBP £ per set
18966	N/a	N/a

"Draper *Expert* HI-TORQ" is a trademark of Draper Tools Ltd.

"PZ TYPE" insert bits are compatible with \*Pozi/Supadriv fixing systems.

\*Pozi/Supadriv are registered trademarks of European Industrial Services Ltd.

"Draper TX-STAR" insert bits are compatible with †Torx fixing systems.

†Torx is the registered trademark of Camcar/Textron Inc.



Stock No.	Chk Digit	Description	FARNELL CODE
18966	3	75 PIECE 1/4" SQ. DR. COMBINED SOCKET SET	106088

#### DRAPER BULLETS

these need to be kept to a minimum, in order of priority.

- Metric and AF sizes
- 37 "Draper *Expert* HI-TORQ" 6 point sockets
- 8 accessories
- Bit holder and 29 assorted bits
- Chrome vanadium steel hardened, tempered, chrome plated and polished for corrosion protection

BRAND: **DRAPER EXPERT** BARCODED **YES**