



**SCATTERGOOD
& JOHNSON LTD**



ELECTRICAL ENGINEERING AND FLUID CONTROL DISTRIBUTORS

Ferraz

Modular Fuse Holders

- * Modular design
- * Din rail mounting
- * Basic fuse holders fit up to 2 microswitches
- * Unipolar fuse holders fit 1 microswitch and/or an indicator
- * Provision for Locking
- * IP 20
- * Standards IEC 269-2-1 / 947-3
- * Approvals Lloyds / Veritas



MSC/Q216674

MSC/W219784

MSC/Y201317

MSC/M215659

MSC10: FUSE 10 x 38 MM (In max: 32A / Vn max: 690V)

Part No.	Price Each	Description	Fuse Link Size Ref.	Fuse Type
MSC10/Q216674	£2.52	SINGLE POLE Basic Fuse Holder	10 x 38 mm	GL HRC 0.5-32A AM 0.5-25A
MSC10/W219784	£5.13	SINGLE POLE Basic Fuse Holder with Integral		
MSC10/Y201317	£7.45	SINGLE POLE + NEUTRAL Basic Fuse Holder		
MSC10/M215659	£13.51	TRIPLE POLE Basic Fuse Holder		
MSC10/G215125	£0.44	Fuse Holder Assembly Pins 2 Poles		
MSC10/Q216145	£0.62	Fuse Holder Assembly Pins 3 Poles		



CMS14/F222990

CMS14/P217708

CMS14/J212091

CMS14/N200779

*Accepts all accessories

CMS14: FUSE 14 x 51 MM (In max: 50A / Vn max: 690V)

Part No.	Price Each	Description	Fuse Link Size Ref.	Fuse Type
CMS141/F222990	£9.60	SINGLE POLE Basic Fuse Holder	14 x 51 mm	GL HRC 2-50A AM 2-50A
CMS14/P217708	£11.23	SINGLE POLE Unipolar* Fuse Holder		
CMS143/J212091	£31.31	TRIPLE POLE Basic Fuse Holder		
CMS14/N200779	£36.36	TRIPLE POLE Unipolar* Fuse Holder		
CMS14/Z218223	£0.77	Fuse Holder Assembly Pins		



CMS22/E213628

CMS22/G201325

CMS22/Z216682

CMS22/W215667

*Accepts all accessories

CMS22: FUSE 22 x 58 MM (In max: 125A / Vn max: 690V)

Part No.	Price Each	Description	Fuse Link Size Ref.	Fuse Type
CMS221/E213628	£13.76	SINGLE POLE Basic Fuse Holder	22 x 58 mm	GL HRC 4-125A AM 4-125A
CMS22/G201325	£15.58	SINGLE POLE Unipolar* Fuse Holder		
CMS223/Z216682	£43.95	TRIPLE POLE Basic Fuse Holder		
CMS22/W215667	£49.22	TRIPLE POLE Unipolar* Fuse Holder		
CMS22/L211058	£0.78	Fuse Holder Assembly Pins		