Toggle Switch Sealed DPDT

multicomp PRO

RoHS

Compliant

Specifications

Mechanical Life : 30,000 make-and-break cycles. Contact Resistance : 20 m Ω max. initial @ 2-4V DC

Insulation Resistance : 1,000 M Ω min.

Dielectric Strength : 1,500 Vrms min.@sea level.

Operating Temperature : -30°C to 85°C.

Rating : 12 Amps @125/250V AC.

Materials


Contact Plating : Silver Terminal Plating : Nickel


Case : Diallyl phthalate (Nylon) (UL94V-0).


Actuator : Brass, Chrome Plated.


Bushing : Zin+Silicon Terminal/Contact : Copper

Diagram










Without locking ring.

With standard locking ring.

PANEL MOUNTING



Dimensions: Inches (Millimetres)

Switch Function


	Pos.1	Pos.2	Pos.3
Model		.	4
MP1HAD2T1B1M1N1S-5	ON	NONE	ON
Term. Comm.	2-3 5-6		2-1 5-4
Schematic	2 Comm. 3	N/A	2 Comm. 3 P


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro





Toggle Switch Sealed DPDT


multicomp PRO













SI. No.	Part Name	Qty.	Material	
1	15/32 Inch Nuts	2	C3604, Nickel Plated	
2	Locking Ring	1	SPCC, Zinc Blue Plated	
3	Locking Washer	'	Stainless Steel.	
4	M3.5 Screw		C3604, Nickel Plated	
5	Washer	6	Stainless Steel	
6	Spring Washer		Stairliess Steel	

Part Number Table

Description	Part Number
Toggle Switch, Screw Terminal, ON-NONE-(ON), DPDT	MP1HAD2T1B1M1N1S-5

Dimensions: Inches (Millimetres)

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

