Product datasheet

Specifications





Power Logic PM5000 - 5RD Remote display 96 x 96 mm monochrome

METSEPM5RD

Main

Range	PowerLogic
Product Or Component Type	Remote display
Device Application	Human-machine dialogue application
Range Compatibility	PowerLogic PowerLogic PM5000
Display Type	Backlit LCD

Complementary

Display Colour	Monochrome	
Display Resolution	128 x 128 pixels	
Display Size	67 x 62.5 mm	
Information Displayed	Power Energy consumption Harmonic distortion Frequency Voltage Current	
Messages Display Capacity	6 lines Graphic objects (bargraph, button, light)	
Local Signalling	Communication: LED (green) Programming indication: LED (amber)	
Control Type	4 x push-button	
Connector Type	RJ45	
Mounting Mode	Flush-mounted	
Mounting Support	Framework remote display	
Width	96 mm	
Height	96 mm	
Embedding Depth	21 mm	
Projecting Depth	27 mm	

Environment

Ip Degree Of Protection	IP52 conforming to IEC 60529
Relative Humidity	595 % at 37 °C
Operating Altitude	03000 m
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	10 cm
Package 1 Length	10 cm
Package 1 Weight	320 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information