

Product data sheet

Specifications



CANopen preassembled cable - for CANopen bus - 1 m - 1 RJ45, 1 female SUB-D 9

VW3M3805R010

Product availability : Stock - Normally stocked in distribution facility

Main

Range of Product	CANopen
Range compatibility	Modicon LMC058 Lexium 28 Modicon M238 Lexium SD3 Modicon M258 Magelis XBT GC, GT/GK with control
Bus type	CANopen
Accessory / separate part category	Connection accessory
Accessory / Separate Part Type	Connecting cable
Product or Component Type	CANopen preassembled cable
Accessory / separate part destination	CANopen bus

Complementary

Cable length	3.28 ft (1 m)
Electrical Connection	2 connectors
Connector Type	1 RJ45 1 female SUB-D 9 with integrated line terminator
Net Weight	0.17 lb(US) (0.077 kg)

Ordering and shipping details

Category	18263-LEXIUM 32 ACCESSORIES
Discount Schedule	PC51
GTIN	3389119214599
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.000 cm)

Package 1 Width	5.12 in (13.000 cm)
Package 1 Length	7.09 in (18.000 cm)
Package 1 Weight	2.47 oz (70.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	17.10 lb(US) (7.758 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	800
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	154.46 lb(US) (70.064 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)