

Product data sheet

Specifications



PLUG BI 32A FIL LG 250MM

AK5PC33

Product availability : Stock - Normally stocked in distribution facility

Main

Range Linergy

Product name HK

Product or Component Type Plug outlet

Poles description 3P

[Ith] conventional free air thermal current 32 A

I²t on activation 200000 A².s

Number of points 2

Number of cables 3 0.01 in² (4 mm²)

Cable length 0.82 ft (0.25 m)

Quantity per Set Set of 6

Complementary

[Ui] rated insulation voltage 600 V CSA
600 V UL
690 V IEC 60439-1

Peak current 25 kA

Width 1.42 in (36 mm)

Height 1.81 in (46 mm)

Depth 1.50 in (38 mm)

Net Weight 0.10 lb(US) (0.045 kg)

Environment

Standards IEC 60439

Product Certifications DNV
LRROS (Lloyds register of shipping)
CSA
UL

Ordering and shipping details

Category 22623-PANEL BUS (AK5)

Discount Schedule I11

GTIN	3389110576856
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.00 in (12.7 cm)
Package 1 Width	5.31 in (13.5 cm)
Package 1 Length	6.10 in (15.5 cm)
Package 1 Weight	2.01 oz (57 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	5.31 in (13.5 cm)
Package 2 Width	5.00 in (12.7 cm)
Package 2 Length	6.10 in (15.5 cm)
Package 2 Weight	14.07 oz (399 g)
Unit Type of Package 3	S04
Number of Units in Package 3	96
Package 3 Height	11.81 in (30 cm)
Package 3 Width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	15.93 lb(US) (7.226 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
-----------------	-----------

Recommended replacement(s)