# **Product data sheet**

Specification





Head for pilot light, Harmony 9001K, metal, without cap, 30mm, 110...120V

9001KP1

## Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Head for pilot light	
Device Short Name	К	

# Complementary

,		
Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Cap/Operator Or Lens Colour	Without cap	
Bulb Base	BA 9s	
Light Block Supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz	
Shape Of Screw Head	Round	
Light Source	Incandescent bulb	
Operating Mode	Normal	
[Us] Rated Supply Voltage	110120 V	
Light Block Supply	Via integral transformer	
Supply Frequency	5060 Hz	
Size	30 mm	

#### **Environment**

Product Certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	7.84 oz (222.26 g)
Unit Type Of Package 2	PAL

Number Of Units In Package 2	1200
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	601.00 lb(US) (272.609 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations