



Complete control station, Harmony 9001B, 2 push buttons ON/OFF, Maintained Contact, 5A, 600V AC, 2NO, NEMA 7/9

9001BR216

### Main

Range Of Product	Harmony 9001B	
Product Or Component Type	Complete control station	
Device Short Name	9001BR	
Control Station Application	Two functions	
Colour Of Base Of Enclosure	Grey	

## **Complementary**

Material	Cast zinc	
Marking	CE	
Type Of Operator	maintained	
Control Station Composition	1 push-button, black, white ON 1 push-button, red, white OFF	
Contacts Type And Composition	1 NO + 1 NC	
Mechanical Durability	5000000 cycles	
[le] Rated Operational Current	5 A 600 V, AC	
Device Mounting	Surface	
Type Of Installation	Indoor	

#### **Environment**

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Nema Degree Of Protection	NEMA 7/9
Product Certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Environmental Characteristic	Hazardous location

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	13.97 in (35.484 cm)	
Package 1 Width	5.50 in (13.97 cm)	
Package 1 Length	35.48 in (90.129 cm)	
Package 1 Weight	3.69 lb(US) (1.674 kg)	



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information