

Product data sheet

Specifications



power cable - between servomotor
BSH and servodrive - 4 x 2.5 mm2 -
5 m

VW3M5102R50

Product availability : Stock - Normally stocked in distribution facility

Main

| | |
|---------------------------------------|--|
| Product or Component Type | Power cable |
| Accessory / Separate Part Type | Preamsembled power cordset |
| Accessory / separate part category | Connection accessory |
| Product compatibility | Servo motor BMH, 2 5.51 in (140 mm)) Servo motor BMH, 3 5.51 in (140 mm)) |
| Accessory / separate part destination | Between servo motor and servo drive |
| Range Compatibility | Lexium 05 Lexium 32 |
| Cable length | 16.40 ft (5 m) |
| Cable composition | 4 x 2.5 mm² + 2 x 1 mm² |

Complementary

| | |
|-----------------------|--|
| Electrical connection | Connector - industrial M23 servo motor side Free end servo drive side |
| Net Weight | 3.68 lb(US) (1.67 kg) |

Ordering and shipping details

| | |
|-------------------|-----------------------------|
| Category | 18263-LEXIUM 32 ACCESSORIES |
| Discount Schedule | PC51 |
| GTIN | 3389119207355 |
| Returnability | No |
| Country of origin | DE |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.11 in (7.900 cm) |
| Package 1 Width | 15.16 in (38.500 cm) |
| Package 1 Length | 15.51 in (39.400 cm) |

| | |
|------------------------------|---------------------------|
| Package 1 Weight | 3.86 lb(US) (1.749 kg) |
| Unit Type of Package 2 | P06 |
| Number of Units in Package 2 | 30 |
| Package 2 Height | 29.53 in (75.000 cm) |
| Package 2 Width | 31.50 in (80.000 cm) |
| Package 2 Length | 23.62 in (60.000 cm) |
| Package 2 Weight | 143.01 lb(US) (64.870 kg) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Recommended replacement(s)