

25 Wood splitting wedge

Forged, with groove.

Code	No.	L mm		P.UNIT
8648380	25	240	2000	1



646 E-H Double faced club hammer ROT BAND-PLUS

Dutch pattern

Hammer head forged from high-quality special steel, coated with black epoxy powder. Contoured ash or hickory handle DIN 5135, additionally with long and hardened steel sleeve.

The sleeve, tapered collar, fixing plate and wood screw bond the hammer head and wood handle into one unit.

Spare handles see club hammer No. 620.

Code	No.	L mm			P.UNIT
8682130	646 E-1000	260	1000	1190	6
8683100	646 E-1250	260	1250	1410	6
8683290	646 E-1500	280	1500	1725	6
8683370	646 E-2000	300	2000	2000	6
8683020	646 H-1000	260	1000	1190	6
8682720	646 H-1250	260	1250	1410	6
8682800	646 H-1500	280	1500	1725	6
8682990	646 H-2000	300	2000	2240	6



46 E-H Double faced club hammer

Dutch pattern

Head only (46) or with ash handle (46 E) or hickory handle (46 H). Hammer head forged, carefully hardened and tempered, coated with black epoxy powder, striking face and pein polished, accurate chamfer. Spare handles see club hammer No. 20.

Code	No.	L mm			P.UNIT
8666360	46-1000		1000	1000	6
8666440	46-1250		1250	1250	6
8666520	46-1500		1500	1500	6
8666600	46-2000		2000	2000	6
8667090	46 E-1000	260	1000	1190	6
8667170	46 E-1250	260	1250	1410	6
8667250	46 E-1500	280	1500	1725	6
8667330	46 E-2000	300	2000	2000	6
8668060	46 H-1000	260	1000	1190	6
8668140	46 H-1250	260	1250	1410	6
8668220	46 H-1500	280	1500	1725	6
8668300	46 H-2000	300	2000	2240	6



620 E-H Club hammer ROT BAND-PLUS

Forged head DIN 6475 made from high-quality special steel, coated with black epoxy powder, carefully hardened and tempered. Contoured ash or hickory handle DIN 5135, supplementary with long and hardened steel sleeve. The sleeve, tapered collar, fixing plate and wood screw bond the hammer head and wood handle into one unit.

Code	No.	L mm			P.UNIT
8886990	620 E-1000	260	1000	1190	6
8887020	620 E-1250	260	1250	1410	6
8887100	620 E-1500	280	1500	1735	6
8887290	620 E-2000	300	2000	2240	6
8887370	620 H-1000	260	1000	1190	6
8887450	620 H-1250	260	1250	1410	6
8887530	620 H-1500	280	1500	1735	6
8887610	620 H-2000	300	2000	2240	6



E 620 Spare handle ROT BAND-PLUS

Ash or hickory. With hardened steel sleeve, fixing plate, tapered collar and wood screw.

For all club hammers according to DIN 6475.

Code	No.	L mm		P.UNIT
8678100	E 620 E-1000	260	190	1
8749650	E 620 E-1250	260	190	1
8676670	E 620 E-1500	280	225	1
8676750	E 620 E-2000	300	240	1
8677210	E 620 H-1000	260	190	1
8749730	E 620 H-1250	260	190	1
8677480	E 620 H-1500	280	225	1
8677560	E 620 H-2000	300	240	1

