

45 ft. (14 m) HDMI Signal Booster - 4K 60Hz

Product ID: HDBOOST4K2



Use this 4K HDMI signal booster to amplify your HDMI signal and extend it 45 ft. (14 m) using HDMI cabling.

When you're extending HDMI over distances using standard video cabling, higher resolutions from your HDMI 2.0 devices can become unavailable after a few short feet. With this signal extender you can ensure that HDMI 2.0 resolutions up to UHD 4K at 60Hz are available even at distances up to 45 ft. (14 m). You can achieve even longer distances at lower refresh rates - up to 4K at 30Hz, at up to 100 ft. (30 m).

The signal booster works by connecting two HDMI certified cables, each up to 22.5 ft. (7 m) in length, to either side of the signal booster.

With its compact design, the HDMI signal amplifier is easy to hide, for a discreet installation. By extending your video signal using HDMI certified cables, the inline booster is a cost-effective alternative to more expensive extension systems that require the installation of a CAT5 or CAT6 cabling infrastructure.

Support for a variety of extension distances makes the 4K repeater perfect for multi-device deployment across large institutions, such as boardrooms in corporate offices, classrooms in schools, or waiting rooms in hospitals, as these applications may require varied distances in different rooms.

HDBOOST4K2 is backed by a 2-year StarTech.com warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Amplify your 4K video signals up to 45 ft. (14 m)
- Boost the signal strength of your HDMI video signals in classrooms, offices and boardrooms
- Avoid network cabling to extend video signals, using this extender with standard HDMI cables

Features

- **BOOST YOUR SIGNAL:** Use this repeater to amplify your 4K HDMI signal extending it 45 ft. using certified HDMI cables. Operating System Independent, no extra drivers or software required.
- **4K RESOLUTION SUPPORT:** Enjoy astonishing picture quality with support for 4K 60Hz at up to 45 ft. away from your video source.
- **AUDIO SUPPORT:** This HDMI inline repeater supports 7.1 surround sound audio for an complete AV solution.
- **SMALL FOOTPRINT:** Designed to be compact, this HDMI amplifier is easy to setup and can be hidden away for a discreet installation.
- **INDUSTRY-LEADING SUPPORT:** StarTech.com offers a 3-year warranty and free lifetime technical support on this 4K HDMI video signal booster, and has been the choice of IT professionals and businesses for over 30 years.

Hardware

Warranty	2 Years
AV Input	HDMI
AV Output	HDMI
Cabling	HDMI
Audio	Yes
Rack-Mountable	No
Daisy-Chain	No

Performance

Video Revision	HDMI 2.0
Max Distance	14 m / 45 ft
Wide Screen Supported	Yes
Bandwidth	18Gbps
Audio Specifications	DTS Dolby Digital

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Power

Power Source	Not Included (not required for standard applications)
Input Voltage	5V DC
Output Voltage	5 DC
Plug Type	USB Micro-B
Power Consumption (In Watts)	<2.5

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5% to 90% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	1.1 in [2.8 cm]
Product Width	2.0 in [5.2 cm]
Product Height	0.5 in [1.4 cm]
Weight of Product	0.5 oz [15.0 g]

Packaging Information

Package Quantity	1
Package Length	6.6 in [16.8 cm]
Package Width	5.6 in [14.2 cm]
Package Height	1.3 in [3.2 cm]

Shipping (Package) Weight	4.0 oz [112.0 g]
------------------------------	------------------

What's in the Box

Included in Package	1 - HDMI Signal Booster
	1 - 1 ft [30 cm] Micro USB Power Cable
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***