





Safety switch, heavy duty, fused, viewing window, NEMA 4X, 240V, 60A, 3 pole, neutral installed, ground lugs

VH322NDSGL

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	Neutral (factory installed)	
Number Of Poles	3	
Current Rating	60 A	
Voltage Rating	250 V DC 240 V AC	
Enclosure Rating	NEMA 4X stainless steel 304	
Motor Power Hp	ower Hp 3 hp at 240 V AC 50-60 Hz for 1 phase motors 7.5 hp at 240 V AC 50-60 Hz for 3 phase motors 10 hp at 240 V AC 50-60 Hz for 1 phase motors 15 hp at 240 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC	

Complementary

Short-Circuit Current	10 kA for H, K, J or R without fuse rejection clips 200 kA for R with fuse rejection clips 200 kA for J	
Fuse Type	H or K R or J	
Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	4-wire (3PH + N)	
Wire Size	AWG 14AWG 3 copper AWG 12AWG 3 aluminium	
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 3) 45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 50 lbf.in (5.65 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)	
Depth	5.384 in (136.75 mm)	
Width	7.22 in (183.39 mm)	
Height	14.93 in (379.22 mm)	
Net Weight	13.23 lb(US) (6 kg)	

Grounding Kit	Factory installation
Service Entrance	Suitable service entrance for USA Suitable service entrance for Mexico

Environment

Certifications UL listed file E2875

Ordering and shipping details

Category	US10DE100010	
Discount Schedule	0DE1	
Gtin	3606485893495	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.50 in (13.97 cm)
Package 1 Width	8.87 in (22.542 cm)
Package 1 Length	16.62 in (42.227 cm)
Package 1 Weight	13.23 lb(US) (6 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov