



GUC3100

USB 3.0 GigaLinq - Gigabit Ethernet Adapter over USB

The USB 3.0 GigaLinq Ethernet Adapter plugs into your MacBook Air, Ultrabook, Microsoft Surface, Chromebook, or other laptop's USB 3.0 port and allows you to connect a standard RJ-45 Ethernet cable to deliver Internet and network access at up to Gigabit (1000Mbps) speed.



Features

- Bring Gigabit network connection speed to devices without an Ethernet port using a SuperSpeed USB 3.0 connection
- Turn your USB 3.0 port into a Gigabit (10/100/1000Mbps) connection
- Powered by USB, no external power supply needed
- Perfect travel companion for MacBook® Air, Ultrabook®, Microsoft Surface™, Chromebook™ or other laptop
- Compact design slips easily into any computer bag, backpack or briefcase

Ultrabook is a trademark of Intel Corporation in the U.S. and/or other countries. Microsoft and Surface are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. © 2015 Google Inc. All rights reserved. Chromebook™ is a trademark of Google Inc.

Requirements

PC

- Windows® Vista, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
- USB 3.0 port

Mac

- Mac OS 10.7-10.15
- USB 3.0 port

Package Contents

- 1 x GUC3100 USB 3.0 GigaLinq
- 1 x Installation CD
- 1 x Quick Start Guide
- 1 x Warranty Card



Specifications

FUNCTION	GUC3100	DIMENSIONS	GUC3100
Connectors (Input)	RJ45	Unit Dimensions	
Connectors (Output)	USB A 3.0	Height	0.82" (2.1cm)
LEDs		Length	11.45" (29.1 cm)
On Line	Green Light On: Ready to Link, Yellow Light Flashing: Data is Transmitting	Depth	1.14" (2.9 cm)
Transfer Rate	10/100/1000Mbps	Inner Pack	
Network Protocol	10/100/1000 MB LAN	Height	3.74" (9.5cm)
Network Interface	RJ-45 Ethernet 10base-T/100base-TX/1000base-T	Length	1.37" (3.5cm)
Operating System Support	Windows® Vista, Windows® 7, Windows® 8, Windows® 8.1, Mac OS X 10.7+	Width	9.05" (23cm)
Environment		Inner Pack Qty.	6
Operation Temperature	50F - 104F	Unit Package Dimensions	
Storage Temperature	14F - 176F	Height	3.7" (9.5cm)
Power Mode	USB Bus Power 5V	Width	5.51" (14cm)
		Depth	1.37" (3.5cm)
		Master Carton	
		Height	10" (26cm)
		Width	18.8" (48cm)
		Depth	7.2" (18.5cm)
		Master Carton Qty.	24
		Weight	
		Master Carton Wt.	6.6 lbs (3 kg)
		Inner Pack Wt.	1.65lb (0.75 kg)
		Unit Pack Wt.	0.20lb (0.09kg)
		Unit Wt.	0.10lb (.045kg)