



GUH304P

Powered 4 Port USB 3.0 Hub

While today's laptops are lighter and more compact than ever, that savings in size comes at the cost of fewer USB ports to connect your accessories. With the IOGEAR met(AL) Hub series you can instantly expand your USB connectivity with 4 SuperSpeed USB 3.0 ports, allowing you to reclaim your connectivity.



Features

- 4-Port SuperSpeed USB 3.0 Hub with up to 5Gbps data transfer rate plus mobile device charging
- Up to 10x faster than USB 2.0
- Aluminum housing designed to match Macbook computers
- Compatible with Mac and Windows
- Backwards compatible with USB 2.0, 1.1, and 1.0 devices*
- Supports overcurrent protection
- Power adapter included
- Plug-n-Play - no driver or software needed

*Device must be plugged into a USB 3.0 port in order to achieve SuperSpeed rates

Requirements

- Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
- Mac OS X10.2+
- Linux
- USB 3.0 port

Package Contents

- 1 x GUH304P
- 1 x Power Adapter
- 1 x Quick Start Guide
- 1 x Warranty Card



Specifications

FUNCTION	GUH304P	DIMENSIONS	GUH304P
Operating System Requirements		POP Information	
Windows	Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10	10" Peg Hook	4
		6" Peg Hook	2
Mac	Mac OS X10.2+	Unit Dimensions	
Linux	Linux	Height	.75" (1.9cm)
Connectors		Length	4.4" (11.2cm)
USB	USB 3.0	Depth	1.42" (3.6cm)
Power Input Rating		Inner Pack	
Per AC Power Inlet, 50/60Hz	DC5V@4A	Height	7.1" (18cm)
Power Output Rating		Length	8.5" (21.5cm)
Total AC Power Outlet, 50/60Hz	DC5V@2A	Width	13" (33cm)
		Inner Pack Qty.	6
USB Specification	3.0, 2.0, and 1.1	Unit Package Dimensions	
Transfer Rate	Up to 5Gbps	Height	6.0" (15.3cm)
Ports	4 x USB 3.0	Length	5.7" (14.5cm)
LEDs		Depth	2.6" (6.5cm)
Data	Blue	Master Carton	
Operating Temperature	32 ~ 104F (0 ~ 40C)	Height	13.9" (35.2cm)
Storage Temperature	14 - 158F (-10 ~ 70C)	Width	17.6" (44.8cm)
Housing		Depth	14.5" (36.8cm)
Case	Aluminum alloy	Master Carton Qty.	24
		Weight	
		Master Carton Wt.	17.3lb (7.8kg)
		Inner Pack Wt.	3.75lb (1.7kg)
		Unit Pack Wt.	.53lb (.24kg)
		Unit Wt.	.15lb (.07kg)