

# Product datasheet

Specifications



## Mounting plate in galvanized steel, thickness 15 mm For boxes of H225W175 mm

Local distributor code:  
387529071

NSYAMP2419TB

EAN Code: 3606480166099

### Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting location	Back studs
Mounting plate description	Plain
Range compatibility	Thalassa Thalassa TBS Thalassa Thalassa TBP
Device composition	1 mounting plate
Material	Galvanised steel

### Complementary

Fixing mode	By screws - screw type M4 self tapping - on back studs location
Height	Nominal: 241 mm Real: 1685 mm
Width	Nominal: 194 mm Real: 215 mm
Thickness	1.5 mm
Net weight	0.12 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.200 cm
Package 1 Width	17.000 cm
Package 1 Length	21.500 cm
Package 1 Weight	400.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	4.000 cm
Package 2 Width	19.500 cm
Package 2 Length	23.000 cm

Package 2 Weight	4.000 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	480
Package 3 Height	23.000 cm
Package 3 Width	100.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	214.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

---

✓ Toxic Heavy Metal Free

---

✓ Mercury Free

---

✓ Rohs Exemption Information Yes

---

## Certifications & Standards

**Reach Regulation**

[REACH Declaration](#)

---

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

---

**China Rohs Regulation**

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

---

**Environmental Disclosure**

[Product Environmental Profile](#)

---

**Circularity Profile**

No need of specific recycling operations

---