

# WIREFOX-E 10 - Stripping tool



1212706

<https://www.phoenixcontact.com/gb/products/1212706>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

## Product description

Insertable stripping blades: 1212151 WIREFOX 4/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212152 WIREFOX 10/SB

## Your advantages

- Flexible, adjustable limit stop for the stripping length
- Stripping tool with ergonomically shaped pliers
- Practical integrated wire cutter
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters

## Commercial data

Item number	1212706
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH3121
Product key	BH3121
Catalog page	Page 405 (C-3-2019)
GTIN	4046356783613
Weight per piece (including packing)	254.4 g
Weight per piece (excluding packing)	253 g
Customs tariff number	82032000
Country of origin	SE

# WIREFOX-E 10 - Stripping tool

1212706

<https://www.phoenixcontact.com/gb/products/1212706>



## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

### Product properties

Product type

Stripping tool

Application

Standard

### Connection data

#### Conductor connection

Cross section range, metric

0.02 mm<sup>2</sup> ... 10 mm<sup>2</sup> (Stripping range)

1.5 mm<sup>2</sup> (Cutting zone)

Cross section range AWG

34 ... 8 (Stripping range)

16 (Cutting zone)

Stripping length

2 mm ... 18 mm

### Dimensions

Width

20 mm

Height

90 mm

Length

191 mm

### Material specifications

Color

black/green

# WIREFOX-E 10 - Stripping tool

1212706

<https://www.phoenixcontact.com/gb/products/1212706>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1212706>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# WIREFOX-E 10 - Stripping tool



1212706

<https://www.phoenixcontact.com/gb/products/1212706>

## Classifications

### ECLASS

ECLASS-11.0	21043706
ECLASS-12.0	21043706
ECLASS-13.0	21043706

### ETIM

ETIM 9.0	EC002109
----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# WIREFOX-E 10 - Stripping tool



1212706  
<https://www.phoenixcontact.com/gb/products/1212706>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)