

Computer Cable

DB25P Male to DB25P Male




RoHS
Compliant



Specifications

Molded connector end requirements	: A) Inner mold using PE B) Aluminium foil wrpc to connector C) PVC - 45P, Platinum grey
Cable	: [28AWG (7 / 0.12) * 25C + AL / MY + DW (7 / 0.16)] TIN Insulation : PP, OD = $\varnothing 0.78 \pm 0.03\text{mm}$ Jacket : PVC, OD = $\varnothing 7\text{mm} \pm 0.15\text{mm}$ Colour : Platinum gray
Thumbscrew	: Male 4mm \times 47mm, Nickel plating
Connectors	: DB25P Pin Male, Nickel plating, Insulator Colour : Blue

Diagram



No.	Description	Qty.
1	283-25C+D+A-Grey22-7	-
2	CDS-25P(Blue)	2
3	SOL-Wire-Full-Tin-1.0	0.5
4	PE-5321	17
5	PVC-Grey 22/50	64
6	SRW-E31.5/Grey 22	4

PIN ASSIGNMENT			
P1	P2	P1	P2
1	1	14	14
2	2	15	15
3	3	16	16
4	4	17	17
5	5	18	18
6	6	19	19
7	7	20	20
8	8	21	21
9	9	22	22
10	10	23	23
11	11	24	24
12	12	25	25
13	13	S	S

Pin Outs								
DB25 Male	Wire Colour	OB25 Male	DB25 Male	Wire Colour	OB25 Male	DB25 Male	Wire Colour	OB25 Male
1	Black	1	10	Red	10	19	Light-Green	19
2	Brown	2	11	Black / White	11	20	Pink	20
3	Red	3	12	Brown / White	12	21	Pink / Black	21
4	Orange	4	13	Red / White	13	22	Gray / Black	22
5	Yellow	5	14	Orange / White	14	23	Orange / Black	23
6	Green	6	15	Yellow / Black	15	24	Red / Black	24
7	Blue	7	16	Green / White	16	25	Green / Black	25
8	Purple	8	17	Blue / White	17	Shell	-	Shell
9	White	9	18	Purple / White	18	-	-	-

Dimensions : Millimetres

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands



Computer Cable

DB25P Male to DB25P Male



Part Number Table

Description	Length		Part Number
	(Inches)	(mm)	
DB25P Male to DB25P Male	72 ±1	1,829 ±25.4	SPC19935
	120 ±2	3,048 ±50.8	SPC19929
	300 ±3	7,625 ±76.2	SPC19932

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

