

160 i/6 Rack Screwdriver set Kraftform Plus Series 100 + Rack, 6 pieces

Kraftform Plus – Series 100 VDE



EAN:	4013288027887	Size:	285x210x55 mm
Part number:	05006145001	Weight:	641 g
Article number:	160 i/6 Rack	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- "Take it easy" tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away
- Lasertip tips for more secure fit in the screw head

6-piece screwdriver set with individually tested, insulated screwdrivers as per IEC 60900. Individual testing in a water bath at 10,000 volts so as to ensure safe working at the permitted voltage of 1,000 volts. Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Partially Lasertip: the tip literally bites itself into the screw head and prevents any slipping. "Take it easy" Tool Finder: colour coding according to profile and size. The anti-roll feature prevents any bothersome rolling away at the workplace. Including a rack for storage.

Web link

https://products.wera.de/en/tools_for_electricians_kraftform_plus_series_100_vde_160_i_6 Rack.html


Wera - 160 i/6 Rack
05006145001 - 4013288027887

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



Our screwdrivers are tested for dielectric strength under a 10,000 volt load to make sure that their most important property, their insulation, has been exhaustively tested. Each individual Wera VDE screwdriver is subjected to this test to guarantee safe working up to 1,000 volts.

Reduced contact pressure



Wera Lasertip reduces the contact pressure required and enhances force transfer - meaning less screwdriving effort is required. Screwdriving becomes safer and easier.

Lasertip



A precisely-focused laser creates a sharp-edged surface structure. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle




Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

"Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

Web link

https://products.wera.de/en/tools_for_electricians_kraftform_plus_series_100_vde_160_i_6_rack.html

Wera - 160 i/6 Rack
05006145001 - 4013288027887

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

160 i/6 Rack Screwdriver set Kraftform Plus Series 100 + Rack, 6 pieces

Kraftform Plus – Series 100 VDE



Set contents:

162 i PH VDE Insulated screwdriver for Phillips screws, PH 1 x 80 mm



05006152001	1x	PH 1 x 80 mm
05006154001	1x	PH 2 x 100 mm

160 i VDE Insulated screwdriver for slotted screws, 0.4 x 2.5 x 80 mm



05006100001 ¹⁾	1x	0.4 x 2.5 x 80 mm
05006110001 ¹⁾	1x	0.6 x 3.5 x 100 mm
05006115001	1x	0.8 x 4 x 100 mm
05006120001	1x	1 x 5.5 x 125 mm

1) without Lasertip

Web link

https://products.wera.de/en/tools_for_electricians_kraftform_plus_series_100_vde_160_i_6_rack.html

Wera - 160 i/6 Rack
05006145001 - 4013288027887

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de