


**RoHS  
Compliant**



## Specifications

Connector to Connector : IDC Receptacle to IDC Receptacle  
Colour : Grey

## Diagram



No.	Description
1	2.5mm IDC Socket with Strain Relief
2	1.27mm Flat Cable 28AWG; Colour Grey

Dimensions : Millimetres

## Part Number Table

Description	No. of Position	IDC Socket		Flat Cable Assembly	Part Number
		Dim. A	Dim. B	Length	
IDC Receptacle Both End	6P	12.3	5.08	50mm	MP012785
		12.3	5.08	100mm	MP012786
		12.3	5.08	150mm	MP012787
		12.3	5.08	200mm	MP012788
		12.3	5.08	250mm	MP012789
		12.3	5.08	300mm	MP012790
	8P	14.84	7.62	50mm	MP012791

# Flat Cable Assemblies

**multicomp**PRO

Description	No. of Position	IDC Socket		Flat Cable Assembly	Part Number
		Dim. A	Dim. B	Length	
IDC Receptacle Both End	8P	14.84	7.62	100mm	MP012792
		14.84	7.62	150mm	MP012793
		14.84	7.62	200mm	MP012794
		14.84	7.62	250mm	MP012795
		14.84	7.62	300mm	MP012796
	10P	17.38	10.16	50mm	MP012797
		17.38	10.16	100mm	MP012798
		17.38	10.16	150mm	MP012799
		17.38	10.16	200mm	MP012800
		17.38	10.16	250mm	MP012801
		17.38	10.16	300mm	MP012802
	14P	22.46	15.24	50mm	MP012803
		22.46	15.24	100mm	MP012804
		22.46	15.24	150mm	MP012805
		22.46	15.24	200mm	MP012806
		22.46	15.24	250mm	MP012807
	16P	22.46	15.24	300mm	MP012808
		25	17.78	50mm	MP012809
		25	17.78	100mm	MP012810
		25	17.78	150mm	MP012811
		25	17.78	200mm	MP012812
	20P	25	17.78	250mm	MP012813
		25	17.78	300mm	MP012814
		30.08	22.86	50mm	MP012815
		30.08	22.86	100mm	MP012816
		30.08	22.86	150mm	MP012817
	24P	30.08	22.86	200mm	MP012818
		30.08	22.86	250mm	MP012819
		30.08	22.86	300mm	MP012820
		35.16	27.94	50mm	MP012821
		35.16	27.94	100mm	MP012822
	26P	35.16	27.94	150mm	MP012823
		35.16	27.94	200mm	MP012824
		35.16	27.94	250mm	MP012825
		35.16	27.94	300mm	MP012826
		37.7	30.48	50mm	MP012827
		37.7	30.48	100mm	MP012828

# Flat Cable Assemblies

**multicomp**PRO

Description	No. of Position	IDC Socket		Flat Cable Assembly	Part Number
		Dim. A	Dim. B	Length	
IDC Receptacle Both End	26P	37.7	30.48	150mm	MP012829
		37.7	30.48	200mm	MP012830
		37.7	30.48	250mm	MP012831
		37.7	30.48	300mm	MP012832
	30P	42.78	35.56	50mm	MP012833
		42.78	35.56	100mm	MP012834
		42.78	35.56	150mm	MP012835
		42.78	35.56	200mm	MP012836
		42.78	35.56	250mm	MP012837
		42.78	35.56	300mm	MP012838
	34P	47.86	40.64	50mm	MP012839
		47.86	40.64	100mm	MP012840
		47.86	40.64	150mm	MP012841
		47.86	40.64	200mm	MP012842
		47.86	40.64	250mm	MP012843
		47.86	40.64	300mm	MP012844
	40P	55.48	48.26	50mm	MP012845
		55.48	48.26	100mm	MP012846
		55.48	48.26	150mm	MP012847
		55.48	48.26	200mm	MP012848
		55.48	48.26	250mm	MP012849
		55.48	48.26	300mm	MP012850
	50P	68.18	60.96	50mm	MP012851
		68.18	60.96	100mm	MP012852
		68.18	60.96	150mm	MP012853
		68.18	60.96	200mm	MP012854
		68.18	60.96	250mm	MP012855
		68.18	60.96	300mm	MP012856
	60P	80.88	73.66	50mm	MP012857
		80.88	73.66	100mm	MP012858
		80.88	73.66	150mm	MP012859
		80.88	73.66	200mm	MP012860
		80.88	73.66	250mm	MP012861
		80.88	73.66	300mm	MP012862
	64P	85.96	78.74	50mm	MP012863
		85.96	78.74	100mm	MP012864
		85.96	78.74	150mm	MP012865

Description	No. of Position	IDC Socket		Flat Cable Assembly	Part Number
		Dim. A	Dim. B	Length	
IDC Receptacle Both End	64P	85.96	78.74	200mm	MP012866
		85.96	78.74	250mm	MP012867
		85.96	78.74	300mm	MP012868

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.