# **Product datasheet**

Specifications





"Wall mounted steel enclosure, PanelSeT S3D, plain door, with mounting plate, 600x400x200mm, IP66, IK10"

Local distributor code:

392866350 NSYS3D6420P

EAN Code: 3606480159329

#### Main

Mairi	
Range	PanelSeT
Product name	PanelSeT S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	600 mm
Enclosure nominal width	400 mm
Enclosure nominal depth	200 mm
Door type	Plain
Mounting plate description	Plain
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	1 body 1 mounting plate 1 door with lock 1 cable gland plate

### Complementary

body type	Single piece body
	Gutter-shaped front rail double sheet thickness
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
lock type	3 points lock, 3 mm double-bar
Accessibility for operation	Front
Removable parts	Door by hinges
	Cable gland plate by screws
	Mounting plate by fixing element
Material	Enclosure: steel
	Mounting plate: galvanised steel
Surface finish	Enclosure: epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035)
Standards	IEC 62208
product certifications	GL
	UL
	cUL
	DNV
	BV

Net weight 13 kg

#### **Environment**

NEMA degree of protection	NEMA 4X/13
IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP66 conforming to IEC 60529

# **Packing Units**

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.5 cm
Package 1 Width	42.0 cm
Package 1 Length	61.5 cm
Package 1 Weight	13.306 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	30
Package 2 Height	199.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	411.0 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

## **Product datasheet**

# NSYS3D6420P

**Technical Illustration** 

**Dimensions** 



## **Product datasheet**

## NSYS3D6420P

Offer Marketing Illustration

**Product benefits / Features** 

