Product data sheet

0

Specifications



Earth leads section 6mmÂ², length 160mm, eyelet hole 6,4mm. Packaging unit: 10.

NSYEL166D6

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	PanelSeT	
Anwendung	Multi-purpose	
Product or Component Type	Earthing wire	
Device composition	1 lead	
Quantity per Set	Set of 10	

Complementary

Material	PVC (polyvinyl chloride) green and yellow sheath Brass and copper alloy terminal	
Fixing mode	Nut and washer - on earth connection	
Length	6.3 in (160 mm)	
Width	0.4 in (10 mm)	
Nominal cross section	0.009 in² (6 mm²)	
Diameter	0.3 in (6.4 mm)	

Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
GTIN	3606480181627	
Returnability	No	
Country of origin	FR	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.4 in (1 cm)
Package 1 Width	4.1 in (10.5 cm)
Package 1 Length	7.9 in (20 cm)
Package 1 Weight	0.5 oz (13 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	7.9 in (20 cm)
Package 2 Width	4.1 in (10.5 cm)
Package 2 Length	0.4 in (1 cm)
Package 2 Weight	4.7 oz (134 g)
Unit Type of Package 3	P12
Number of Units in Package 3	9600
Package 3 Height	22.05 in (56 cm)
Package 3 Width	31.5 in (80 cm)
Package 3 Length	47.2 in (120 cm)
Package 3 Weight	335.3 lb(US) (152.1 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations