



Plain mounting plate H150xW200mm made of galvanised sheet steel

NSYMM12SB

Local distributor code: 397090749

EAN Code: 3606480520518

Main

Range	PanelSeT	
Accessory / separate part category	Mounting accessory	
Product or component type	Mounting plate	
Device application	Multi-purpose	
Enclosure nominal dimensions	-	
Mounting location	Bottom of enclosure	
Mounting plate description	Plain	
Range compatibility	PanelSeT PanelSeT SBM	
Device composition	1 mounting plate	
Material	Galvanised steel	
Surface finish	Metallic	

Complementary

Fixing mode	By 2 screws - screw type Ø5 mm self-tapping screws - bottom of enclosure location	
Permanent permissible load	1.5 kg back of the enclosure	
Height	Nominal: 125 mm	
Width	Nominal: 185 mm Fixing centers: 164 mm	
Surface and useful surface	Nominal: 30000 mm²	
Thickness	1.5 mm	
Net weight	ht 0.254 kg	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	19.000 cm	
Package 1 Width	13.000 cm	
Package 1 Length	0.300 cm	
Package 1 Weight	254.000 g	
Unit Type of Package 2	CAR	
Number of Units in Package 2	30	
Package 2 Height	20.000 cm	

Package 2 Width	16.000 cm	
Package 2 Length	10.500 cm	
Package 2 Weight	7.700 kg	
Unit Type of Package 3	PAM	
Number of Units in Package 3	1500	
Package 3 Height	45.000 cm	
Package 3 Width	100.000 cm	
Package 3 Length	120.000 cm	
Package 3 Weight	399.400 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

NSYMM12SB

Technical Illustration

Dimensions

