

# DISPENSING CONSUMABLES

PART NUMBER	DESCRIPTION	PART NUMBER	DESCRIPTION	PART NUMBER	DESCRIPTION
1125-0001-P10	Needle, SS, 14GA, 0.5"	1125-0020-P50	Needle, SS, 18GA, .1"	1125-0033-P50	Tip, Plastic, Taper, 20GA
1125-0001-P50	Needle, SS, 14GA, 0.5"	1125-0021-P10	Needle, SS, 20GA, .1"	1125-0034-P10	Tip, Plastic, Taper, 22GA
1125-0002-P10	Needle, SS, 15GA, 0.5"	1125-0021-P50	Needle, SS, 20GA, .1"	1125-0034-P50	Tip, Plastic, Taper, 22GA
1125-0002-P50	Needle, SS, 15GA, 0.5"	1125-0022-P10	Needle, SS, 21GA, .1"	1125-0035-P1	Adapter, syringe, 5cc
1125-0003-P10	Needle, SS, 16GA, 0.5"	1125-0022-P50	Needle, SS, 21GA, .1"	1125-0036-P1	Adapter, syringe, 10cc
1125-0003-P50	Needle, SS, 16GA, 0.5"	1125-0023-P10	Needle, SS, 22GA, .1"	1125-0037-P1	Adapter, syringe, 30cc
1125-0004-P10	Needle, SS, 17GA, 0.5"	1125-0023-P50	Needle, SS, 22GA, .1"	1125-0038-P5	Barrel & Stopper, 5cc, 5 pack
1125-0004-P50	Needle, SS, 17GA, 0.5"	1125-0024-P10	Needle, SS, 23GA, .1"	1125-0038-P10	Barrel & Stopper, 5cc, 10 pack
1125-0005-P10	Needle, SS, 18GA, 0.5"	1125-0024-P50	Needle, SS, 23GA, .1"	1125-0039-P5	Barrel & Stopper, 10cc, 5 pack
1125-0005-P50	Needle, SS, 18GA, 0.5"	1125-0025-P10	Needle, SS, 24GA, .1"	1125-0039-P10	Barrel & Stopper, 10cc, 10 pack
1125-0006-P10	Needle, SS, 19GA, 0.5"	1125-0025-P50	Needle, SS, 24GA, .1"	1125-0040-P5	Barrel & Stopper, 30cc, 5 pack
1125-0006-P50	Needle, SS, 19GA, 0.5"	1125-0026-P10	Needle, SS, 25GA, .1"	1125-0040-P10	Barrel & Stopper, 30cc, 10 pack
1125-0007-P10	Needle, SS, 20GA, 0.5"	1125-0026-P50	Needle, SS, 25GA, .1"	1125-0067-P5	Luer Lock Tip Cap, Pack 5
1125-0007-P50	Needle, SS, 20GA, .5"	1125-0027-P10	Needle, SS, 26GA, .1"	1125-0067-P10	Luer Lock Tip Cap, Pack 10
1125-0008-P10	Needle, SS, 21 GA, 0.5"	1125-0027-P50	Needle, SS, 26GA, .1"	1125-0068-P5	Flex Cap for Taper Tip Pack 5
1125-0008-P50	Needle, SS, 21 GA, 0.5"	1125-0028-P10	Needle, SS, 27GA, .1"	1125-0068-P10	Flex Cap for Taper Tip Pack 10
1125-0009-P10	Needle, SS, 22GA, 0.5"	1125-0028-P50	Needle, SS, 27GA, .1"	1125-0069-P5	Needle Cover Cap, Pack 5
1125-0009-P50	Needle, SS, 22GA, 0.5"	1125-0029-P10	Needle, SS, 30GA, .1"	1125-0069-P10	Needle Cover Cap, Pack 10
1125-0010-P10	Needle, SS, 23GA, 0.5"	1125-0029-P50	Needle, SS, 30GA, .1"	1125-0070-P5	3cc Manual Syringe, Pack 5
1125-0010-P50	Needle, SS, 23GA, 0.5"	1125-0030-P10	Tip, Plastic, Taper, 14GA	1125-0070-P10	3cc Manual Syringe, Pack 10
1125-0011-P10	Needle, SS, 24GA, 0.5"	1125-0030-P50	Tip, Plastic, Taper, 14GA	1125-0071-P5	5cc Manual Syringe, Pack 5
1125-0011-P50	Needle, SS, 24GA, 0.5"	1125-0031-P10	Tip, Plastic, Taper, 16GA	1125-0071-P10	5cc Manual Syringe, Pack 10
1125-0012-P10	Needle, SS, 25GA, 0.5"	1125-0031-P50	Tip, Plastic, Taper, 16GA	1125-0072-P5	10cc Manual Syringe, Pack 5
1125-0012-P50	Needle, SS, 25GA, 0.5"	1125-0032-P10	Tip, Plastic, Taper, 18GA	1125-0072-P10	10cc Manual Syringe, Pack 10
1125-0013-P10	Needle, SS, 26GA, 0.5"	1125-0032-P50	Tip, Plastic, Taper, 18GA	1125-0073-P5	1cc Manual Syringe, Pack 5
1125-0013-P50	Needle, SS, 26GA, 0.5"	1125-0033-P10	Tip, Plastic, Taper, 20GA	1125-0073-P10	1cc Manual Syringe, Pack 10
1125-0014-P10	Needle, SS, 27GA, 0.5"	<p>Dispensing consumable products include syringe needles in multiple gauges, plastic tapered tips, syringe adapters, and barrel stoppers.</p>  <p><b>Dispensing Nozzles</b></p>			
1125-0014-P50	Needle, SS, 27GA, 0.5"				
1125-0015-P10	Needle, SS, 30GA, 0.5"				
1125-0015-P50	Needle, SS, 30GA, 0.5"				
1125-0016-P10	Needle, SS, 14GA, .1"				
1125-0016-P50	Needle, SS, 14GA, .1"				
1125-0017-P10	Needle, SS, 15GA, .1"				
1125-0017-P50	Needle, SS, 15GA, .1"				
1125-0018-P10	Needle, SS, 16GA, .1"				
1125-0018-P50	Needle, SS, 16GA, .1"				
1125-0019-P10	Needle, SS, 17GA, .1"				
1125-0019-P50	Needle, SS, 17GA, .1"				
1125-0020-P10	Needle, SS, 18GA, .1"				