




M12 Metric Circular Connector, K Code, Metal, 16A, 05 pins, Female Connector, Female (Power) + Male (Ground) Contact, Straight, Screw Thread, Overmolded, Length 1000mm, IP68 / IP69K

M12K-05BFDM-SL8S01

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A

Shielded: Metal, Non-shielded

Jacket Material: TPU

Certificate: UL2237

You must login first for view the price

Quantity

-


1

+

 Check Stock

 Add to Cart

 Inquiry



[RoHS / REACH / PFOS, PFOA Reports \(/support/rohs-report/\)](/support/rohs-report/)

Mating Pair & Accessories

Connector Type

 Search



CAP-WBDFSMA1
Metric Circular Connector,...
(/product-info/Metric+Circular+Connector/Metric+Series.Accessory/CAP-WBDFSMA1.html)
- 0 +
☐



CAP-WBDFSMA2
Metric Circular Connector,...
(/product-info/Metric+Circular+Connector/Metric+Series.Accessory/CAP-WBDFSMA2.html)
- 0 +
☐



M12K-05BMEM-SL8S01
M12 Metric Circular Connecto...
(/product-info/Metric+Circular+Connector/Metric+Series.M12%28K%29/M12K-05BMEM-SL8S01.html)
- 0 +
☐



M12K-05BMEM-SL8S02
M12 Metric Circular Connecto...
(/product-info/Metric+Circular+Connector/Metric+Series.M12%28K%29/M12K-05BMEM-SL8S02.html)
- 0 +
☐



M12K-05B
M12 Metric Circular Connecto...
(/product-info/Metric+Circular+Connector/Metric+Series.M12%28K%29/M12K-05BMEM-SL8S01.html)
-
☐

Add to Cart

Inquiry

Specifications
Download / CAD
Nominal Current 16A

Connector Type Overmolded
Shielded Metal, Non-shielded
No. of Contacts 05
Connector Gender Female
Backshell Straight
Mating Style Screw Thread
IP Rating IP68 / IP69K
Assembly Style N/A
Net Weight (G)

200.00
Operating voltage 630V
Salt Spray 48h
Coding K
Contact Gender Female (Power) + Male (Ground)
Receptacle Nut Thread N/A
Fasten Style N/A
Wire/Cable Length 1000
Air Permeability N/A

Cable O.D Φ10.0mm
Wire AWG 14 AWG
Panel Thickness N/A
More Options

People Also Bought

 (/product-info/Metric+Circular/M-Series.M12%28K%205BFDM-SL8S01.html) M12K-05BFDM-...	 (/product-info/Ceres/Ceres.M12(K)/ACB-04BFFM-SL7A05.html) ACB-04BFFM-SL7A0...	 (/product-info/X-Lok/X-Lok.StandardSize/BB-03AFMM-QR8E10.html) BB-03AFMM-QR8E1...	 (/product-info/X-Lok/X-Lok.MiddleSize/CB-04BMMA-QL8SP0.html) CB-04BMMA-QL8SP...	 (/product-info/Metric+Circular/M-Series.M12%28A%20SAPFL-SD004.html) MSAP12ML-SAPFL-...
--	--	---	---	---