




**Part Number :** [190440168](#)  
**Product Description :** Krimptite Ring Tongue  
Terminal for 16-14 AWG, Stud Size 5/16",  
24.28mm Length, Carton  
**Series Number :** 19044  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** B-130-56HD



## Documents & Resources


**Drawings**  
[190440168\\_sd.pdf](#)

**3D Models and Design Files**  
[190440168\\_stp.zip](#)

**Specifications**  
[PS-19902-011-001.pdf](#)  
[PS-19902-013-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC  
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Ring and Spade Terminals
Series	19044
Description	Krimptite Ring Tongue Terminal for 16-14 AWG, Stud Size 5/16", 24.28mm Length, Carton
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Type	Ring
UPC	800755060348

#### Agency

CSA	LR18689
UL	E32244

#### Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.250/g
Packaging Type	Carton
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	5/16" (M8)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16

Wire Size mm <sup>2</sup>	1.30-2.00
---------------------------	-----------

---

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup>	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>