


Piggyback Disconnect



Features

- Complete line of the most popular, color coded, vinyl insulated brazed and butted seam terminals
- One piece tin plated barrel construction provides maximum electrical conductivity and corrosion resistance
- V Notches in the barrel provides maximum holding strength and excellent current flow over a wide contact area
- Bending strength is drastically increased due to barrel to pad gusset transition design
- Open-end barrel design permits visual inspection of wire placement prior to crimping
- Strand hang-up is eliminated with the flared and internally funneled sleeve.

Drawing



Advanced Cable Ties Part Number	A IN (mm) +/- .005 (.127mm)	B IN (mm) +/- .005 (.127mm)	C IN (mm) +/- .005 (.127mm)	D IN (mm) +/- .005 (.127mm)	E IN (mm) +/- .005 (.127mm)	F IN (mm) +/- .005 (.127mm)	G IN (mm) +/- .005 (.127mm)	H IN (mm) +/- .005 (.127mm)	I IN (mm) +/- .005 (.127mm)	J IN (mm) +/- .005 (.127mm)	Colour/ Material	Copper Cond. Range
MP015309	.870 (22.10mm)	.410 (10.41mm)	.110 (2.79mm)	.0575 (1.48mm)	.156 (3.96mm)	.160 (4.06mm)	.032 (.81mm)	.310 (7.86mm)	.370 (9.41mm)	.250 (6.35mm)	Red/Vinyl	22-18
MP015310			.140 (3.56mm)	.082 (2.08mm)							Blue/Vinyl	14-14

Part Number Table

Description	Part Number
Red Vinyl Piggyback Disconnect, 100Pk	MP015309
Blue Vinyl Piggyback Disconnect, 100Pk	MP015310

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

