

Product information

00 21 06 M

Tool Case “BIG Basic Move” Mechanic

90 parts



- Equipped with 12 KNIPEX Tools, a total of 90 brand tools
- With a total of 54 inserting options
- Max. payload: 20 kg
- Volume: 33 litres
- Strong, ergonomic handle
- Heavy duty ABS material, black
- Circumferential aluminium frame
- Metal hinges
- Document compartment in the cover
- Two removable tool boards made of dirt-repellent PP twin-fall sheets with 31 tool pockets
- First tool board with ten tool pockets and an elastic strap on the cover side and eleven narrow and one large tool pocket on the base side
- Second tool board with ten tool pockets and an elastic strap on the base side and a document compartment on the cover side
- Base tray, can be fixed by a push button, 70 mm high, can be subdivided by inserts, cover board with 14 large tool pockets
- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Two metal tilting locks and three-digit combination lock for secure closing of the lid
- Label field with two stickers for individual labelling

General

Article No.	00 21 06 M
EAN	4003773086222
Weight	12,800 g
Dimensions	515 x 430 x 280 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	430 mm (350 mm)
Dimension exterior (interior) height mm	280 mm (200 mm)
Dimension exterior (interior) depth mm	515 mm (480 mm)

Content

16 20 50 SB	1 x Folding Knife for Electricians (120 mm)
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) MM
26 12 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) (200 mm)  ⊖
26 22 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) (200 mm)  40° ⊖
70 02 160	1 x Diagonal Cutter (160 mm) 
71 31 200	1 x KNIPEX CoBolt® Compact Bolt Cutter (Ø 5,2 mm) 
74 02 200	1 x High Leverage Diagonal Cutter (200 mm) 

Content

78 61 140	1 x Electronic Super Knips® XL (140 mm) 
86 01 250	1 x Pliers Wrench pliers and a wrench in a single tool (250 mm) 
00 11 01	1 x Knipex KNIPEX TwinKey® Control Cabinet Key for all standard cabinets and shut-off systems (92 mm)
87 01 250	1 x Knipex KNIPEX Cobra® High-Tech Water Pump Pliers (250 mm) 
01114	1 x Stabila Wooden folding rule type 1607, white (2.000 mm)
HP400-12 M	1 x Heyco Combination wrench sets (6/8/10/11/12/13/14/15/16/17/18/19 mm)
101-0300	1 x Picard Locksmith's hammer (300 g)
425 530 6	1 x Rennsteig Pin punch set (Ø 3 mm/4 mm/5 mm/6 mm/8 mm/10 mm)
430 130	1 x Rennsteig Automatic punch (130 mm)
02190	1 x Stabila Spirit level type 70TM (22 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm) 
004018	1 x Wera 8100 SA 8 Zyklop set of metal ratchets 28 parts (1/4")
080150	1 x Wera Screwdriver for slotted screws 335 (0,6 x 3,5 x 100 mm) 
087100	1 x Wera Screwdriver for Phillips® screws 350 PH (PH1 x 80 mm) 
087350	1 x Wera Screwdriver for Phillips® screws 350 PH (PH3 x 150 mm) 
093100	1 x Wera Screwdriver for Pozidriv® screws 355 PZ (PZ1 x 80 mm) 
093150	1 x Wera Screwdriver for Pozidriv® screws 355 PZ (PZ2 x 100 mm) 
093200	1 x Wera Screwdriver for Pozidriv® screws 355 PZ (PZ3 x 150 mm) 
100040	1 x Wera Screwdriver for slotted screws 335 (0,8 x 4,0 x 100 mm) 
118008	1 x Wera Micro screwdrivers for slotted screws 2035 (0,4 x 2,5 x 80 mm) 
118022	1 x Wera Micro screwdrivers for cross recessed Phillips® screws 2050 PH (PH0 x 60 mm) 
170100	1 x Wera Screwdriver for Phillips® screws 917 SPH (PH2 x 100 mm) 
180030	1 x Wera Micro screwdrivers for slotted screws 2035 (0,23 x 1,5 x 60 mm) 
180200	1 x Wera Micro screwdrivers for cross recessed Phillips® screws 2050 PH (PH00 x 60 mm) 
182640	1 x Wera Slotted chisel slotted screws 932 A (1,0 x 5,5 x 100 mm) 

Content	
18266	1 x Wera Slotted chisel slotted screws 932 A 932 A (1,2 x 7,0 x 125 mm)
18268	1 x Wera Slotted chisel slotted screws 932 A 932 A (1,6 x 9,0 x 150 mm)
280050	1 x Wera TORX® Screwdriver 367 (TX10 x 80 mm) ✚
280080	1 x Wera TORX® Screwdriver 367 (TX15 x 80 mm) ✚
280100	1 x Wera TORX® Screwdriver 367 (TX20 x 100 mm) ✚
280120	1 x Wera TORX® Screwdriver 367 (TX25 x 100 mm) ✚
280150	1 x Wera TORX® Screwdriver 367 (TX30 x 115 mm) ✚

Accessories	
00 21 06 LE	Tool Case "BIG Basic Move" empty,

technical change and errors excepted

