

# Portable Digital Thermometer multicomp<sup>PRO</sup>

**RoHS  
Compliant**



## Features

- LED alarm
- Data hold
- Pen-type design
- Max/Min Real-time
- Unit conversion

## Digital Thermometer

This is an IP65 rated thermometer with FDA certified stainless steel probe. It is equipped with a protective shell to prevent accidental skin puncture and burning. With its portable pen-like design, clear backlight display, and auto power off functions, This is a useful temperature measurement tool for cooking, refrigeration, heating, food processing and other applications.

## Specifications

Measurement range	: -40°C to 250°C (-40°F to 482°F)
Accuracy	: ±1°C (-20°C ≤ T < 100°C)
	: ±2°C (T < -20°C; T ≥ 100°C)
	: ±2°F (-4°F ≤ T < 212°F)
	: ±4°F (T < -4°F; T ≥ 212°F)
Minimum Measuring Depth	: 12mm
Sensor	: NTC
Stabilization time	: 20s
Resolution	: 0.1°C (0.1°F)
Battery Duration	: 12h
Operating temperature	: 0°C to +40°C (32°F to +104°F)
Storage temperature	: -20°C to +60°C (-4°F to +140°F)
Operating humidity	: <RH80% (No condensable)

## General Characteristics

Battery	: 3V Battery (CR1632)
Display	: 26.6mm × 10.6mm
Colour	: White and Grey
Net Weight	: 50.8g
Dimensions	: 190mm × 29.5mm × 15.5mm
Standard accessories	: Battery
Warranty	: 03 years

## Part Number Table

Description	Part Number
Digital Thermometer, -40°C to +250°C	MP780428

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp<sup>PRO</sup>**