

Product Specification PDF

Date	Correct as of 19th Feb 2025
Brand	Jokari
Product	T20075
Description	Jokari AS Interface Pro
Barcode	4011391200753
Commodity code	8203200000
Country of origin	DE



Features & Benefits	<p>~ Automatic wire stripper for AS-Interface cables with PUR, TPE or FR-PVC insulation. ~ Full protection for the internal conductors, unlimited stripping length, with optical length scale 15</p> <ul style="list-style-type: none">- 18- 20mm. ~ Tested with cables from Gebauer&Griller: ~ AS-Interface BUS 2 x 1,5 mm² TPE 90301, 80479, 90302,80489 ~ AS-Interface BUS 2 x 1,5 mm² FR-PVC 110612, 110614 ~ AS-Interface BUS highflex 2 x 1,5 mm² FR-PUR 21806, 107364, 75244, 107366 ~ AS-Interface BUS Long Distance highflex 2 x 2,5 mm² FR-PUR 143740, 143742 ~ No adjustments required. ~ Spare blades available.
Health & Safety	Never use tool on or near Live electrical circuits

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	0
Width mm	102mm	0	0	-
Depth mm	28mm	0	0	-
Height mm	166mm	0	0	-
Weight	120g	-	0	0
Packaging Information	Card use	Backing Card	0	-
	Card gms	12	0	0
	Plastic use	Clamshell blister	0	-
	Plastic gms	9	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0

Product Specification PDF

Date	Correct as of 19th Feb 2025
Brand	C.K Tools
Product	T4915PZ2
Description	VDE Screwdriver Spare Blade PZ2
Barcode	5013969070217
Commodity code	8207903000
Country of origin	TW



Features & Benefits	<p>~ VDE approved</p> <ul style="list-style-type: none">- individually tested to 10.000V for safe working up to 1000V ~ According to EN 60900, VDE0682/201 ~ Toughened alloy steel blades for exceptional durability ~ For C.K Screwdriver handles T4915
Applicable Standards	BS EN 60900 , VDE 682/201, ASTM-F 1505, DIN ISO 8764
Health & Safety	Users are advised to regularly examine their VDE tools, Even the slightest damage can compromise the insulation integrity and potentially expose the user to the risk of injury or even death
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	50
Width mm	10	50	125	220
Depth mm	10	15	205	140
Height mm	150	200	55	280
Weight	26	41	461	2.4
Packaging Information	Card use	Backing card	box	Carton
	Card gms	7	59	197
	Plastic use	Clamshell blister	0	-
	Plastic gms	8	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0

Product Specification PDF

Date	Correct as of 19th Feb 2025
Brand	C.K Tools
Product	T4915S55
Description	VDE Screwdriver Spare Blade SL 5.5mm
Barcode	5013969070170
Commodity code	8207903000
Country of origin	TW



Features & Benefits	<p>~ VDE approved</p> <ul style="list-style-type: none">- individually tested to 10.000V for safe working up to 1000V ~ According to EN 60900, VDE0682/201 ~ Toughened alloy steel blades for exceptional durability ~ For C.K Screwdriver handles T4915
Applicable Standards	BS EN 60900 , VDE 682/201, ASTM-F 1505, ISO 2380-2
Health & Safety	Users are advised to regularly examine their VDE tools, Even the slightest damage can compromise the insulation integrity and potentially expose the user to the risk of injury or even death
Warranty	C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	50
Width mm	10	50	125	220
Depth mm	10	15	205	140
Height mm	150	200	55	280
Weight	26	41	461	2.4
Packaging Information	Card use	Backing card	box	Carton
	Card gms	7	59	197
	Plastic use	Clamshell blister	0	-
	Plastic gms	8	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0