

USB Power Adapter

Multi Head Type C Plug

multicomp PRO

**RoHS
Compliant**



Features

- Interchangeable AC Heads: US, EU, UK, AUS
- DOE Level VI Efficiency
- Overcurrent and Short Circuit Protection
- Type C USB Socket
- Multi Head Wall Plug Adapter
- PD Power USB Protocol – Auto Detec
- 1 Year Warranty
- Approvals: CE, UKCA & FCC

Specification Table

Characteristics		Part Number	
		MP009260	MP009261
Output	DC Voltage	5V/9V/12V/15V/20V	
	Rated Current	3A/3A/2.5A/2A/1.5A	3A/3A/3A/3A/3A
	Current Range	3 Amp. (Max.)	
	Rated Power	30 Watt	60 Watt
	Ripple & Noise	100mVp-p max	300mVp-p max
	Output Regulation	±5%	
	Output Connector	USB C Socket	
Input	Voltage Range	90V AC to 264V AC	
	Frequency Range	50Hz to 60Hz	
	Input Current	0.8 Amp. (Max.)	1.3 Amp. (Max.)
	Inrush Current	40 Amp. (Max.)	
	Standby Power	0.1W (Max.)	
	Leakage Current	0.25 Amp. (Max.)	
	Input Connector	UK, EU, & US AC Heads	
Environment	Operating Temp	0°C to +40°C	
	Cooling	Convection	
	Temperature Coefficient	0.05%/°C	
	Humidity	5~95%RH (non-condensing)	
	Storage Temp	-20°C to +60°C	
Safety & EMC	Safety Standards	UL/CUL 62368-1, GS/TUV EN62368-1	
	EMC Emissions	EN55032, FCC Part 15 Class B	
General	Dimensions	53mm × 53mm × 28mm	65.5mm × 65.5mm × 29mm
	Weight	35g	55g

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO