




PART NO.

E0508 Series

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Ramya	25/9/09	Jagan	25/9/09	Farnell	9/10/09



Dimensions : Millimetres

Specifications:

Maximum electric current	:	AWG	22
		Amperes	9
Maximum electrical rating	:	105°C, 600V.	
Insulation material	:	Nylon.	
Insulation colour	:	French colour	: White.
		German colour	: Orange.
		Din colour	: White.
Connector material	:	Copper tube.	
Wire range	:	22AWG (0.50mm <sup>2</sup> ).	
Connector surface treatment	:	Tin plated.	

Part Number Table

Description	Part Number
Ferrule, Insulated, 0.5mm, PK100	E0508-ORANGE
	E0508-WHITE

<http://www.farnell.com>  
<http://www.newark.com>  
<http://www.cpc.co.uk>

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2009.

**TOLERANCES:**  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

<b>DRAWN BY:</b>	<b>DATE:</b>
Ramya	25/09/09
<b>CHECKED BY:</b>	<b>DATE:</b>
Jagan	25/09/09
<b>APPROVED BY:</b>	<b>DATE:</b>
Farnell	09/10/09

<b>DRAWING TITLE:</b>			
<b>Cable Ferrule - Insulated 0.5mm<sup>2</sup></b>			
<b>SIZE</b>	<b>DWG NO.</b>	<b>ELECTRONIC FILE</b>	<b>REV</b>
A	M10002370	9972277-DWG	A
<b>SCALE: NTS</b>		<b>U.O.M.: mm</b>	<b>SHEET: 1 OF 1</b>