



















RoHS
Compliant

Electrical Test

- Open/Short/Intermittence 100% Test
- Dielectric Strength:200 Volts AC 2mA Max/0.02S.
- Insulation Resistance:300V DC/0.02SEC, 10MΩ MIN.
- Conductive Resistance:1-5M:5Ω MAX,5-10M:10Ω MAX.



Dimensions : Millimetres

P1	WH/OR	OR	WH/GR	GR	BL	WH/BL	WH/BR	BR	SHEEL
	1	2	3	6	4	5	7	8	
COLOR									
PAIR									
COLOR									
P2	1	2	3	6	4	5	7	8	SHEEL
	WH/OR	OR	WH/GR	GR	BL	WH/BL	WH/BR	BR	

No.	Part Number	Description	Unit
1	Cable	CAT5E FTP 26AWG(7C/0.16BC+HDPE0.90)*4P+ D:7C/0.12CCA+AL-FOLL+Black PVC OD5.7±0.2MM	M
2	Connector	RJ45 8P8C FU*Njckl plating on iron shell	2PCS
3	Model	Black PVC	G

Part Number Table

Description	Part Number
Ethernet Cable, CAT5E, STP, White, 0.5M	MP015531
Ethernet Cable, CAT5E, STP, White, 1M	MP015532
Ethernet Cable, CAT5E, STP, White, 2M	MP015533
Ethernet Cable, CAT5E, STP, White, 3M	MP015534
Ethernet Cable, CAT5E, STP, White, 5M	MP015535
Ethernet Cable, CAT5E, STP, Black, 0.5M	MP015541
Ethernet Cable, CAT5E, STP, Black, 1M	MP015542
Ethernet Cable, CAT5E, STP, Black, 2M	MP015543
Ethernet Cable, CAT5E, STP, Black, 3M	MP015544
Ethernet Cable, CAT5E, STP, Black, 5M	MP015545
Ethernet Cable, CAT5E, STP, Blue, 1M	MP015546
Ethernet Cable, CAT5E, STP, Blue, 2M	MP015547
Ethernet Cable, CAT5E, STP, Blue, 5M	MP015548
Ethernet Cable, CAT5E, STP, Green, 1M	MP015549
Ethernet Cable, CAT5E, STP, Green, 2M	MP015550
Ethernet Cable, CAT5E, STP, Green, 3M	MP015551
Ethernet Cable, CAT5E, STP, Yellow, 2M	MP015552
Ethernet Cable, CAT5E, STP, Yellow, 5M	MP015553

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.