10/02/2010

tesa® 4120 hand - Industry Product F...

| tesa worldwide Extranet login Sitemap Search Contact www.tesa.com | | | |
|------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| INDUSTRIES OFFICE & AT HOME ADHESIVE TAPE RANGE COMPANY HINTS & TIPS | | | |
| _ Automotive | < back to search results | | PRODUCTS INDUSTRY |
| _ Automotive Refinishing | PRODUCT INFORMATION | | |
| _ Corrugated Cardboard Industry | tesa® 4120 hand | 1 particular and a second | Type in a search term or select a category from the dropdow ns. |
| _ Craftsmen and Trades | General purpose carton sealing tape | 4120 | |
| _ Electronics | | | |
| Fairs & Exhibitions | and the second se | All Assortments | |
| Flexographic Printing | | | All Applicationfields |
| _ Furniture Industry | | | Reset Search |
| - | | | |
| Marine Industry | | Q | |
| _ Paper & Print | | | Contact details: |
| Packaging & Logistics | Product Description | | General: + 44 (0)1908 211333 |
| _ Painting and Decorating | tesa® 4120 is a packaging tape based on a PVC-film backing and a natural rubber | | C/S Dept: + 44 (0)1908 500333 |
| _ Trims & Profile Producers | adhesive. | | |
| _ Security, Brand Protection & Identification | tesa® 4120 can be used on manual and automatic sealing equipment. | | Industries |
| _ Solar Industry | Main Applications tesa® 4120 is used for manual sealing of cartons of medium weight. | | Adhesive Tape Guide Know your adhesive tapes, from Double Sided Tape, Cloth Tape, Safety Tape, Masking Tape to Splicing Tape, Packaging Tape, Strapping Tape and more >> |
| _ Health Markets | | | |
| _ Product Range | | | |
| _ tesanet Distributors | Technical Data | | |
| | Backing material | PVC film | |
| | Type of adhesive | natural rubber | |
| | Total thickness | 49 µm | |
| | Adhesion to steel | 2 N/cm | |
| | Elongation at break | 75 % | |
| | Tensile strength | 43 N/cm | |
| | Properties | | |
| | Manual application | yes | |
| | Low noise unwinding | yes | |
| | Printability | ++ | |
| | Evaluation across relevant tesa assortment: ++ very goo | od, + good, o medium, - low | |
| | tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you. | | |
| | back to top ↑ | | |
| | Print view Bookmark | | |
| | | | |