

Datasheet for 76650-0137

General Information

Kit Part Number:	76650-0137
Connector Type:	Wire-to-Board
Solution:	Off the Board Connectors
Molex Family:	Mini Mi II™
Certificates:	N/A
Country of Origin:	Kit assembled in U.S.A

Specifications

Circuit Size:	14, 18, 2, 20, 5, 8
Current Rating:	1.5A
Mounting Style:	SMT (Surface Mount Technology)
Orientation:	IDT Vertical Headers, Receptacles
Pitch:	1.25mm (.049")
Tool Included:	No
Voltage Rating:	100V
Wire Gauge (AWG):	28-26

Product Highlights

Mini Mi II™ wire harness system is designed for high-density harness applications. Mini Mi II™ provides the same 1.5 amperes of current as similar 2.00mm (.079") pitch systems, but in a more compact design. Molex's Integrated Product Division provides the new Mini Mi II™ system in both wire-to-board and wire-to-wire options with different custom lengths and wire configurations enabling multi-branch harnessing configurations, similar to Molex's existing 2.00mm (.079") pitch Mi II™ system. The system saves about 45% of PCB space compared to 2.00mm Mi II™. Mini Mi II™ is available in 2 to 40 circuits in single/dual row and SMT/through-hole styles.

Features and Benefits

- 1.5 amps meets office automation standards
- Internal positive lock for secure retention
- IDT housing for cost effective termination

Applications

- Security devices
- Car audio, car multimedia, car HVAC
- Office equipment
- Set-up boxes

<http://www.molexkits.com>

Bill of Materials

Molex Part No.	Description	Quantity
55450-1469	1.25mm (.049") Pitch Mi II™ Header, Vertical, Surface Mount, 14 Circuits	5
54596-0210	1.25mm (.049") Pitch Mini Mi II IDT Receptacle, 2 Circuits	10
54596-0510	1.25mm (.049") Pitch Mini Mi II IDT Receptacle, 5 Circuits	10
54596-0810	1.25mm (.049") Pitch Mini Mi II IDT Receptacle, 8 Circuits	5
54596-1410	1.25mm (.049") Pitch Mini Mi II IDT Receptacle, 14 Circuits	5
54596-1810	1.25mm (.049") Pitch Mini Mi II IDT Receptacle, 18 Circuits	5
54596-2010	1.25mm (.049") Pitch Mini Mi II IDT Receptacle, 20 Circuits	5
55450-0269	1.25mm (.049") Pitch Mi II™ Header, Vertical, Surface Mount, 2 Circuits	10
55450-0569	1.25mm (.049") Pitch Mi II™ Header, Vertical, Surface Mount, 5 Circuits	10
55450-0869	1.25mm (.049") Pitch Mi II™ Header, Vertical, Surface Mount, 8 Circuits	5
55450-1869	1.25mm (.049") Pitch Mi II™ Header, Vertical, Surface Mount, 18 Circuits	5
55450-2069	1.25mm (.049") Pitch Mi II™ Header, Vertical, Surface Mount, 20 Circuits	5

Recommended Molex Tool

Molex Part No.	Description
----------------	-------------