

Shuttleworth Road, Elms Industrial Estate, Bedford. MK41 0EP UK TEL +44(0)1234 330077 FAX +44(0)1234 330088 E-mail sales@dagnall-electronics.com

Iss 1 09/06/03

1 of 4

PRODUCT DATASHEET

20VA CHASSIS MOUNTED TRANSFORMER



- Designed, Manufactured and tested in accordance with BS3535, EN60742*, EN61558*, EN60950.
- Single 230V or Dual 115V Primaries.
- 4800V isolation Primary Secondary
- CE Marked.
- Comprehensive choice of Secondary Voltages.
- Flame Retardant materials to **UL94-V0**.
- Fully shrouded double section construction.

Weight	0.55	Kg
Typical Regulation	12	%
Frequency	50/60	Hz
Max Ambient	25	°C
Bobbin Material	UL94-V0 Class "B" 130°C	

*requires additional over-current /over-temperature protection.

Please see sheet 2 for part numbers.

THIS DOCUMENT IS THE PROPERTY OF DAGNALL ELECTRONICS LIMITED WHICH HOLDS THE COPYRIGHT IN THE DRAWING AND ALL THE DESIGN RIGHTS IN THE PRODUCT OR COMPONENTS DESCRIBED. ANY INFORMATION SHALL NOT BE COPIED, REPRODUCED OR DIVULGED TO A THIRD PARTY NOR SHALL THE PRODUCT OR COMPONENTS BE MADE, COPIED OR REPRODUCED OR ITS EXISTENCE DISCLOSED TO A THIRD PARTY WITHOUT THE PRIOR CONSENT IN WRITING OF DAGNALL ELECTRONICS LIMITED. IN THE INTEREST OF TECHNICAL IMPROVEMENT AND/OR CUSTOMER SERVICE DAGNALL ELECTRONICS RESERVES THE RIGHT TO INTRODUCE MODIFIED SPECIFICATIONS TO ANY OF THE PRODUCTS ILLUSTRATED OR DESCRIBED IN THIS DATASHEET. E&OE



Shuttleworth Road, Elms Industrial Estate, Bedford. MK41 0EP UK TEL +44(0)1234 330077 FAX +44(0)1234 330088 E-mail sales@dagnall-electronics.com

Iss 1 09/06/03

2 of 4

Part Numbers

Part No	Primary	Secondary	Recommended Secondary Fuse
D3040	230V	6+6V	2AT
D3041	230V	9+9V	1AT
D3042	230V	12+12V	1AT
D3043	230V	15+15V	0.8AT
D3044	115+115V	6+6V	2AT
D3045	115+115V	9+9V	1AT
D3046	115+115V	12+12V	1AT
D3047	115+115V	15+15V	0.8AT


Please see sheets 3 and 4 for dimensions, pin outs and connection information.

Shuttleworth Road, Elms Industrial Estate, Bedford. MK41 0EP UK
TEL +44(0)1234 330077 FAX +44(0)1234 330088
E-mail sales@dagnall-electronics.com
Issue 1. 09/06/03


PRODUCT DATASHEET

20VA CHASSIS MOUNTED TRANSFORMER

Outline Drawing 230V Version



Outline Drawing Dual 115V Version




THIS DOCUMENT IS THE PROPERTY OF DAGNALL ELECTRONICS LIMITED WHICH HOLDS THE COPYRIGHT IN THE DRAWING AND ALL THE DESIGN RIGHTS IN THE PRODUCT OR COMPONENTS DESCRIBED. ANY INFORMATION SHALL NOT BE COPIED, REPRODUCED OR DIVULGED TO A THIRD PARTY NOR SHALL THE PRODUCT OR COMPONENTS BE MADE, COPIED OR REPRODUCED OR ITS EXISTENCE DISCLOSED TO A THIRD PARTY WITHOUT THE PRIOR CONSENT IN WRITING OF DAGNALL ELECTRONICS LIMITED. IN THE INTEREST OF TECHNICAL IMPROVEMENT AND/OR CUSTOMER SERVICE DAGNALL ELECTRONICS RESERVES THE RIGHT TO INTRODUCE MODIFIED SPECIFICATIONS TO ANY OF THE PRODUCTS ILLUSTRATED OR DESCRIBED IN THIS DATASHEET. E&OE

Shuttleworth Road, Elms Industrial Estate, Bedford. MK41 0EP UK TEL +44(0)1234 330077 FAX +44(0)1234 330088 E-mail sales@dagnall-electronics.com Issue 1. 09/06/03


PRODUCT DATASHEET

20VA CHASSIS MOUNTED TRANSFORMER


Connection Diagrams for D3040



Connection Diagrams for D3044 - 230V supply



Connection Diagrams for D3044 - 115V supply



THIS DOCUMENT IS THE PROPERTY OF DAGNALL ELECTRONICS LIMITED WHICH HOLDS THE COPYRIGHT IN THE DRAWING AND ALL THE DESIGN RIGHTS IN THE PRODUCT OR COMPONENTS DESCRIBED. ANY INFORMATION SHALL NOT BE COPIED, REPRODUCED OR DIVULGED TO A THIRD PARTY NOR SHALL THE PRODUCT OR COMPONENTS BE MADE, COPIED OR REPRODUCED OR ITS EXISTENCE DISCLOSED TO A THIRD PARTY WITHOUT THE PRIOR CONSENT IN WRITING OF DAGNALL ELECTRONICS LIMITED. IN THE INTEREST OF TECHNICAL IMPROVEMENT AND/OR CUSTOMER SERVICE DAGNALL ELECTRONICS RESERVES THE RIGHT TO INTRODUCE MODIFIED SPECIFICATIONS TO ANY OF THE PRODUCTS ILLUSTRATED OR DESCRIBED IN THIS DATASHEET. E&GE