

## VideoMate E750 Dual DVB-T PCIe

### PCIe Dual DVB-T TV Card with Power Up Scheduling and Windows Media Center Remote



#### Introduction

Compro VideoMate E750 is a fast PCIe dual DVB-T TV tuner card, which brings clear digital terrestrial TV broadcasts to your desktop PC and lets you view 2 main channels at the same time. It turns your computer into a home entertainment center by bringing you digital TV viewing and personal digital video recording capabilities. VideoMate E750 also comes with the certified Windows Media Center remote which gives users the control of Windows Media Center and ComproDTV.

The included ComproDTV software features DVB-T TV watching/recording, channel surfing, timeshifting, single/multiple still frames capture, brightness/saturation/contrast/hue/sharpness adjustment in each TV channel and exclusive S5(shutdown)/S4(hibernation)/S3(standby) mode power up schedule recording. It also provides the advanced Picture In/Out Picture functions which allow users to watch up to 6 live TV windows and playback video files at once. The Video Desktop function lets users to stream live TV shows as wallpaper and use other applications at the same time.

To enhance the usability of Windows Vista/7 and Windows Media Center, VideoMate E750 also offers an array of useful functions. ComproDTV Gadget Tool provides live TV view and playback list with click of a button on the Windows SideBar. The schedule recording list from Windows Media Center Electronic Programming Guide can be integrated to ComproDTV for an easier schedule recording control. In addition, VideoMate E750 is bundled with Corel DVD MovieFactory 5 SE for DVD authoring. With the bundled Microsoft certified remote for Windows Media Center and powerful features, VideoMate E750 PCIe TV card is undoubtedly your best digital TV card choice.

#### Key Features and Benefits

- Dual DVB-T digital terrestrial TV reception
- Bundle with Windows Media Center remote to control Windows Media Center and ComproDTV
- ComproDTV software with Vista Gadget and Windows Media Center schedule recording list integration
- S5/S4/S3 mode Power Up Scheduled Recording
- Convenient Remote Controlled Power On/Off
- Support SDTV and 1080i HDTV (where available)
- Timeshift for the instant replay and pause live TV
- Advanced PIP/POP features can open up to 2 main channel, 3 sub channel windows and also playback 1 recorded video files at the same time
- Video Desktop can stream live TV shows as wallpaper
- Single/sequential still frame captures and remote snapshot
- Supports H.264, MPEG-2 and Transport Stream record/playback
- Digital TV support EPG, subtitle, & Teletext (where available, not support MHEG-5 in UK)
- Certified for Windows 7 32/64Bit

#### Hardware

- Advanced silicon digital TV tuner x 2
- Silicon digital TV demodulator and PCIe bridge
- Shielding cover for superior EMI resistance
- Support 6, 7, 8 MHz in digital TV
- PCI Express x1 interface and low-profile card design
- Microsoft certified remote control for Windows Media Center
- Card dimensions: 112 x 64 mm

#### Connectors

- DVB-T signal input (I-type connector)
- IR receiver connector
- Power switch connector (2-pin x 2)

#### ComproDTV 4.5

- Watch digital TV on your PC
  - Watch TV in full screen or in a window
  - Timeshifting lets you watch TV on your own terms
  - Channel surfing for multiple channels preview
  - Advanced PIP/POP feature and Video desktop
  - Customizable each channel color and audio settings
  - Customizable channel order and my favorite list
  - Single and sequentially still frame captures
- Flexible schedule recording for your favorite shows
  - Integrates the scheduling list from Windows Media Center to ComproDTV scheduler
  - Supports H.264 and MPEG-2 formats recording
  - Supports TS (Transport Stream) digital TV recording
- View recorded video files

#### Bundled Software

- ComproDTV 4.5 – Watch and record digital TV shows
- Corel DVD MovieFactory 5 SE – Video authoring tool

#### Package Contents

- VideoMate E750 Dual DVB-T PCIe TV tuner card
- Installation CD: ComproDTV 4.5, device drivers, and documentation
- Corel DVD MovieFactory 5 SE software CD
- Start Up Guide
- Windows Media Center remote and batteries
- IR receiver
- Power switch cable (2-pin, female)
- Low-profile bracket (silver)

#### Product Requirements

- CPU
  - P4 2.0 GHz for TV viewing, DVD-quality recording
  - P4 3.0 GHz(SSE 2) for HDTV/TS viewing/recording
  - Core 2 Duo 2.0 GHz(SSE 2) for 6 windows PIP/POP
- Memory: 512 MB (1GB recommended)
- Available PCI Express x1 slot
- CD drive for software installation
- Sound card or on-board sound chip
- Graphics Card or on-board graphics supports DirectX 9
- ATX power
- 2-pin power switch connector from system case
- OS: Windows XP SP3, Vista SP1, Win 7 x86/x64
- Digital TV antenna



www.comprousa.com

Tel +886-2-2918-0169 Fax +886-2-2915-2389

E-mail: [sales@comprousa.com](mailto:sales@comprousa.com) E-mail: [press@comprousa.com](mailto:press@comprousa.com)

\*The information in this document is subject to change without notice.