


[INDUSTRIES](#) | [OFFICE & AT HOME](#) | [ADHESIVE TAPE RANGE](#) | [COMPANY](#) | [HINTS & TIPS](#)

- [_ Automotive](#)
- [_ Automotive Refinishing](#)
- [_ Corrugated Cardboard Industry](#)
- [_ Craftsmen and Trades](#)
- [_ Electronics](#)
- [_ Fairs & Exhibitions](#)
- [_ Flexographic Printing](#)
- [_ Furniture Industry](#)
- [_ Marine Industry](#)
- [_ Paper & Print](#)
- [_ Packaging & Logistics](#)
- [_ Painting and Decorating](#)
- [_ Trims & Profile Producers](#)
- [_ Security, Brand Protection & Identification](#)
- [_ Solar Industry](#)
- [_ Health Markets](#)
- [_ Product Range](#)
- [_ tesanet Distributors](#)

[< back to search results](#)

PRODUCT INFORMATION

tesa® 4287

Tensilised strapping tape

**Product Description**

tesa® 4287 is a tensilised polypropylene strapping tape with a natural rubber adhesive system.

tesa® 4287 exhibits good tensile strength with low elongation at the same time. The applied product is highly heat and cold resistant.

Main Applications

Palletising, belting of electronic components, bundling and closure of shipping cartons.

Technical Data

Backing material	MOPP
Type of adhesive	natural rubber
Total thickness	79 µm
Adhesion to steel	4 N/cm
Elongation at break	35 %
Tensile strength	180 N/cm

Properties

Residue free removal	yes
No discolouration (internal)	yes

Evaluation across relevant tesa assortment: ++ very good, + good, o medium, - low

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you.

[back to top ↑](#)
[Print view](#) | [Bookmark](#)

PRODUCTS INDUSTRY

Type in a search term or select a category from the dropdowns.

Contact details:

General: + 44 (0)1908 211333

C/S Dept: + 44 (0)1908 500333

[Contact us](#)

[Adhesive Tape Descriptions](#)

Adhesive Tape Guide

Know your adhesive tapes, from Double Sided Tape, Cloth Tape, Safety Tape, Masking Tape to Splicing Tape, Packaging Tape, Strapping Tape and more >>

