

## ➤ Motorola Talkabout™ T6222 - Two-Way Radio

### ➤ Technical Specifications

Motorola Talkabout™ T6222 two-way radio allows you to stay in touch with your family and friends. It operates on PMR446 frequency. It can be used in any country where PMR446 frequency is authorised, subject to applicable regulations.

The Talkabout™ T6222 radio has been designed to maximise performance and improve transmission range in the field. It is recommended that you do not use the radio closer than 1.5 metres apart because of heavy interference.

- **Channels:** 8
- **Codes:** 38
- **Frequencies:**

1. 446.00625MHz	5. 446.05635MHz
2. 446.01875MHz	6. 446.06875MHz
3. 446.03125MHz	7. 446.08125MHz
4. 446.04375MHz	8. 446.09375MHz
- **Talk Range:** Up to 3km (2 miles) subject to terrain and conditions.
- **Power Output:** 500mW ERP
- **Operating Temperature:** -20 °C to +55 °C
- **Power Source:** 3 AA batteries or NiMH Battery Pack



BatteryLife :	With 3 AA batteries*	With rechargeable NiMH Battery**
Continuous Talktime:	8.2 hours	2.4 hours
Standby time:	130 hours	39 hours
Weight:	163 g	135 g
Height:	152 mm	152 mm
Width:	56 mm	56 mm
Depth:	33 mm	33 mm

\* Typical

\*\* With premium quality alkaline cells. Battery Life with third party AA NiMH/Nicd cells can vary.

- [Talkabout T6222](#)
- [Key Features & Benefits](#)
- [Accessories](#)
- [Get in Contact](#)



## ➤ Motorola Talkabout™ T6222 - Two-Way Radio

### ➤ Key Features & Benefits

Contact your friends with the new Motorola Talkabout™ T6222 two-way radio. Fun and easy to use, this small, colourful radio is the essential accessory for your favourite activity. Simply press the Push-to-Talk button to instantly connect to your group, and with ten programmable call alert tones each caller is easily identified.

The Motorola Talkabout™ T6222 two-way radio is both shock and water resistant so it is every bit as serious about communication as you are about your sport.

- **Cost-free operation**

No licence fee or airtime charges; just drop in 3 batteries (or NiMH Battery pack) and talk.

- **Instant contact**

Just press the push to talk button for instant contact with your group.

- **Handsfree contact**

Voice activated for totally hands-free instant contact.

- **Vibracall®**

Silent alert for discreet operation.

- **Voice scrambling**

Minimises eavesdropping.

- **Easy to use**

The large easy to read screen with user friendly icons shows; channel, code and status of operation.

- **Stylish and colourful**

Stylishly moulded in high-impact polycarbonate in a choice of three colours - yellow, blue and black.

- **Rugged and durable**

Tested for an equivalent of 5 years, it's water and shock resistant, made to operate wherever you are.

- **Lightweight and "wearable"**

The T6222 walkie-talkie fits in the palm of your hand or sits comfortably on your arm or waist.

- **Adaptable**


Choose from a wide range of accessories to adapt your radio to suit your favourite leisure activity.

- **8 channels and 38 codes**

Allows 304 talk combinations.

**1. AA batteries are required but not included.**

**2. Not waterproof**



➤ **Talkabout T6222**

➤ **Technical Specifications**

➤ **Accessories**

➤ **Get in contact**