



MINIATURE DSG

CAT. NO. 583

Very effective sub-miniature de-soldering tool with incorporated safety shield.

SPECIFICATIONS

Overall Dimensions: 154mm x 14mm dia.
 Nozzle Length: 15.5mm
 Nozzle Tip: 3.0mm dia. O.D. x 1.5mm dia. I.D.
 Weight: 33gms
 Spares: Replacement Micro-Nozzles (Pkt of 5)
 CAT. NO. 58302
 Replacement Neoprene Washers (Pkt of 10)
 CAT. NO. 58301





DSG PRF

CAT. NO. 588

Professional de-soldering tool with flexible 3mm dia nozzle. Incorporated safety shield.

SPECIFICATIONS

Overall Dimensions: 250mm x 20mm dia.
 Nozzle Length: 77mm
 Nozzle Tip: 4.5mm dia. O.D. x 3.0mm dia. I.D.
 Weight: 56gms
 Spares: Replacement Flexi-Nozzles (Pkt of 3)
 CAT. NO. 58801




DSG PRS

CAT. NO. 586

Professional de-soldering tool with standard nozzle. Incorporated safety shield.

SPECIFICATIONS

Overall Dimensions: 180mm x 20mm dia.
 Nozzle Length: 13mm
 Nozzle Tip: 5.0mm dia. O.D. x 3.5mm dia. I.D.
 Weight: 56gms
 Spares: Replacement Standard Nozzles (Pkt of 5)
 CAT. NO. 58601



449-011



DSG PRM

CAT. NO. 587

Professional de-soldering tool with micro nozzle and incorporated safety shield.

SPECIFICATIONS

Overall Dimensions: 190mm x 20mm dia.
Nozzle Length: 20mm
Nozzle Tip: 3.0mm dia. O.D. x 1.5mm dia. I.D.
Weight: 56gms
Spares: Replacement Micro-Nozzles (Pkt of 5)
 CAT. NO. 58701





ANTI-STATIC DSG MINIATURE

CAT. NO. 59802

Sub miniature, anti-static de-soldering tool with incorporated safety shield.

SPECIFICATIONS

Overall Dimensions: 155mm x 14mm dia.
Nozzle Length: 15.5mm
Nozzle Tip: 3.0mm dia. O.D. x 1.5mm dia. I.D.
Weight: 35gms
Spares: Replacement Anti-static Micro-Nozzles (Pkt of 5)
 CAT. NO. 59803
 Replacement Neoprene Washers (Pkt of 10)
 CAT. NO. 58301



ANTI-STATIC DSG

CAT. NO. 598

Anti-static de-soldering tool with micro 1.5mm dia. nozzle. Equipped with safety shield.

SPECIFICATIONS

Overall Dimensions: 190mm x 20mm dia.
Nozzle Length: 20mm
Nozzle Tip: 3.0mm dia. O.D. x 1.5mm dia. I.D.
Weight: 60gms
Spares: Replacement Anti-static Micro-Nozzles
 CAT. NO. 59801

