

















## Cordless Telephone Batteries

<b>CTB01-BP1</b> ◆ 3.6V Varta  A Panasonic KX-T3800, KX-T4046A, KX-T4316AL, KX-T4200, Uniden EX-155, EX-200, EX-300, EX-400, EX-422, EX-500, EX-550, AT&T & others Phonepower NHT 300mAh	<b>CTB02-BP1</b> 3.6V Sanyo  C Telstra Freedom 100/200, Sony SPP-55/65, DSE F7022/7033/7025/7026, Panasonic P-P303PA, Shimada F7008/7228/7808, Cobra, AT&T & others 3/N270AA 270mAh	<b>CTB03-BP1</b> ◆ 4.8V Varta  A Uniden XE600, Voca CT1000 & others 2x2/CP300H 300mAh	<b>CTB04-BP1</b> ◆ 3.6V Varta  D DSE, Panasonic, Supercall & others Phonepower NHT 300mAh
<b>CTB05-BP1</b> ◆ 3.6V Varta  A Cobra CP-468S, GME, Shimada F7200, Sony BPT-10, SSP50/60, SPP80/90/510, Toshiba FT-6000/6100/6200/6300/6310/6400, Uniden EX250/350/777 & others Phonepower NHS 300mAh	<b>CTB06-BP1</b> 4.8V Sanyo  B Voca CT7800 & others 4/N270AA 270mAh	<b>CTB07-BP1</b> 3.6V Panasonic  A Cosmo, Panasonic P-P301PA original battery KX-A36A (most), Sony, Toshiba, Uniden XC301/310/315/320/330/340/345/360/610/650/660/680, XE200/300/400/500/700 (BT161) & others 3/P-30AARM 300mAh	<b>CTB08-BP1</b> ◆ 4.8V Varta  Solder Tags ATD, DSE, James Hardie, Uniden XE600, Voca & others 2x2/CP300H 300mAh
<b>CTB09-BP1</b> ◆ 3.6V Varta  B Goldstar GST-1100/1200/GTE-3100, Panasonic, Radio Shack, Shimada F7002/7102/7220, Skyphone SCP-3000 & others 3/V250H 250mAh	<b>CTB10-BP1</b> 3.6V Sanyo  B Audiotone CDL1A/310/450/500/501/FF-995, Cobra, GE, Panasonic P-P302PA, Sanyo (most), Sharp CDL400, Telstra Freedom 120/220/250/320/400/440/450/500/710 & others 3/N270AA 270mAh	<b>CTB11-BP1</b> 3.6V Sanyo  A Access CT880, Cobra, Panasonic KX-A36/P-P501PA, Sharp CL-A40W, South Western Bell, Uniden EX-255/2100/3101/3102/3810/4100/4101/4102/4800 & others 3/N600AA 600mAh	<b>CTB12-BP1</b> 3.6V Sanyo  B Voca CT-3800 & others 3/N270AA 270mAh
<b>CTB13-BP1</b> 4.8V Sanyo  E Tandy & others 4/N270AA 270mAh	<b>CTB14-BP1</b> ◆ 4.8V Varta  F ATD, Tandy & others 4/CP300H 300mAh	<b>CTB15-BP1</b> ◆ 4.8V Varta  E Radio Shack ET400/410, Tandy & others 2X2/CP300H 300mAh	<b>CTB16-BP1</b> 3.6V Sanyo  Green Cap Panasonic Flipphone KX-A37/P-P201PA/KX-T3000, Cobra CF355S 3/N110AA 110mAh

◆ Denotes this battery is Nickel Metal Hydride replacement for original Nickel Cadmium battery. Where only the brand of phone the battery suits is mentioned, you need to consult us for the individual phone model type.

## Battery Connector Guide

 A Bottom	 B Bottom	 C Bottom	 D Bottom	 E Bottom	 F Bottom	 G Bottom	 H Bottom
 A Top	 B Top	 C Top	 D Top	 E Top	 F Top	 G Top	 H Top

# Cordless Phone Batteries

# Cordless Telephone Batteries

<b>CTB17-BP1</b> 3.6V Sanyo  Solder Tags Sanyo CLT-X1 & others 3/N150N 150mAh	<b>CTB18-BP1</b> 4.8V Sanyo  Solder Tags Electra 1000 & others 4/N150N 150mAh	<b>CTB19-BP1</b> 4.8V Sanyo  Solder Tags AT&T, Audiovox, Phillips, Voca CA185 (replace old connector) & others 4/N600AA 600mAh	<b>CTB20-BP1</b> 3.6V Sanyo  Solder Tags DSE F5800/5805/5810/Y1190/MDL789, Panasonic KX-T3806/KX-T3856, Sony SPP-100/200/300, Soundesign & others 3/N600AA 600mAh
<b>CTB21-BP1</b> 4.8V Sanyo  Wire Leads Miscellaneous 4/N150N 150mAh	<b>CTB22-BP1</b> 3.6V Varta  Solder Tags CosmoTR3039/3040, GE, Panasonic KX-T3807/3822R, Uniden & others 3/CP300H 300mAh	<b>CTB23-BP1</b> 3.6V Varta  A Miscellaneous 3/CP300H 300mAh	<b>CTB24-BP1</b> 3.6V Varta  A Goldstar & others 3/V250H 250mAh
<b>CTB25-BP1</b> 3.6V Varta  B Miscellaneous 3/CP300H 300mAh	<b>CTB26-BP1</b> 3.6V Varta  B Cobra & others 3/CP300H 300mAh	<b>CTB27-BP1</b> 3.6V Varta  Solder Tags Cobra Mura & others 3/CP300H 300mAh	<b>CTB28-BP1</b> 4.8V Varta  Solder Tags Uniden & others 3/CP300H 300mAh
<b>CTB29-BP1</b> 3.6V Varta  B Kambrook, Sincoa CP150 & others 3/CP300H 300mAh	<b>CTB30-BP1</b> 3.6V Sanyo  Black Cap Panasonic KX-A38/P-P202PA/KX-T4000/4000MX/4001/4001AL 3/N110AA 110mAh	<b>CTB31-BP1</b> 3.6V Varta  B Belcon, Bowphone, TT Telephone Tech CT630, Voca & others 3/V250H 250mAh	<b>CTB32-BP1</b> 3.6V Panasonic  G Bell South Southwind models, DSE F7020, Radio Shack ET-542/548 & others 3/P-30AARM 300mAh

◆ Denotes this battery is Nickel Metal Hydride replacement for original Nickel Cadmium battery. Where only the brand of phone the battery suits is mentioned, you need to consult us for the individual phone model type.

## Battery Connector Guide




**Be sure to check polarity, size and voltage before installing!**

## Cordless Telephone Batteries

<b>CTB33-BP1</b> 3.6V Sanyo  Akai CP360AUS, Audioline CDL200/400, Avanti Apollo, NEC Flexiphone 50/100, Panasonic P-03RM, Phillips CP-350AUS & others 3/N270AA 270mAh	<b>CTB34-BP1</b> 3.6V Sanyo  Cobra CP-468S, General Electric 2-952Z/5-2109/5-2201B/5-9519, Sony SPP-50/80/SPP-110/SSP-S10 & others 3/N270AA 270mAh	<b>CTB35-BP1</b> 4.8V Sanyo  Audiovox ATT2R, Cobra CP-200/200S, Phonemate 1120/1121/1140, Voxson VX106 & others 4/N600AA 600mAh	<b>CTB36-BP1</b> 3.6V Sanyo  British Telecom Freeline 100/200/300/500, DSE, Matra, Radio Shack, Telstra Freedom 510/520/640 & others 3/N600AA 600mAh
<b>CTB37-BP1</b> 3.6V Varta  Shimasu F700Z, Teac, TT Telephone Tech & others Phonepower NHT 300mAh	<b>CTB38-BP1</b> 4V Master  Sony, SPP-560F/860F/SSP-1010/SPP-2010/SPP-3000 replaces original Sony battery BP-140 4V SLA Battery Sealed Lead Acid 500mAh	<b>CTB39-BP1</b> 3.6V Sanyo  Telstra Freedom 50 & others 3/N270AA 270mAh	<b>CTB40-BP1</b> 3.6V Varta  Uniden XC-630/631/633 3/V150H 150mAh
<b>CTB41-BP1</b> 3.6V Sanyo  DSE F7030, Omni CT-900 Longreach, Uniden DG910 3/N600AA 600mAh	<b>CTB42-BP1</b> 3.6V GP  Omni CT-500 3/GP28AAAM 280mAh	<b>CTB43-BP1</b> 3.6V GP  Eagle 932 3/GP21AAAM 210mAh	<b>CTB44-BP1</b> 3.6V Varta  Panasonic, KX-TG200AL/210AL, KX-TCA14, HHR-P505A 3/VH1200AA 1300mAh
<b>CTB45-BP1</b> 3.6V Varta  Audioline CDL900, Uniden DS71/72, replaces original Uniden battery BT-700 3/VH700AAA 700mAh	<b>CTB46-BP1</b> 3.6V GP  Omni CT-1818 3/GP28AAAM 280mAh	<b>CTB47-BP1</b> 3.6V Varta  Omni CT-906C, CT-910, Piccolo 3/VH700AAA 700mAh	<b>CTB48-BP1</b> 3.6V GP  Uniden DG-900, DGA-900, DGA-940, DGA-1980, EXR-2400, EXR-2460 (replaces original battery BT-990/BP-2499), Toshiba Most FF-8000 Series & SX2000 Series (TRB-6258) 3 x GP60AA 600mAh

◆ Denotes this battery is Nickel Metal Hydride replacement for original Nickel Cadmium battery.  
 Where only the brand of phone the battery suits is mentioned, you need to consult us for the individual phone model type.

## Battery Connector Guide



# Cordless Phone Batteries

# Cordless Telephone Batteries

**CTB49-BP1** 3.6V

GP



Pressure Contact

Telstra Freedom 901, Vtech VT-1711, VT-1721, VT-9108, VT-9111, VT-9115, replaces original battery 80-4134-00-00 and GP (T272)

3 x AA 600mAh

**CTB50-BP1** 3.6V

Panasonic



D

Philips Icana 5350, Telstra Freedom 460

3/P-30AARM 300mAh

**CTB51-BP1** 3.6V

Sanyo



A

Panasonic KX-TG2400, KX-TG2500, KX-TG2550, KXT-TG2570 replaces original battery (HHR-P401)

3/HR-4/5AA 1350mAh

**CTB52-BP1** 3.6V

GP



D

Audioline FF-788, FF-888, FF-988 replaces original battery (GP60AAH3BMX)

3/GP60AAH 600mAh

**CTB53-BP1** 3.6V

GP



B

Audioline CDL1A, CDL100, CDL110, CDL310, CDL450, CDL500, CDL501, FF-894-2, FF-894HS, FF-895, FF-895HS replaces original battery (GP60AAH3BML)

3/GP60AAH 600mAh

**CTB54-BP1** 3.6V

Sanyo



D

Ericsson 230, 260 replaces original DT200 series handset battery

3/HR-AAAU 700mAh

**CTB55-BP1** 3.6V

Sanyo



Pressure Contact

Omni SN-900 EnGenius replaces original battery (SN-91/92)

3/N700AACL 700mAh

**CTB56-BP1** 3.6V

GP



C

Goldtron P-600B DECT replaces original battery (GP60AAH3BMJ) Telstra Freedom 70

3/GP60AAH 600mAh

**CTB57-BP1** 2.4V

Sanyo



A

Panasonic KX-TC1000/1000B/1001/1170/1170AL replaces original battery (P-305PA)

2/N350AAC 350mAh

**CTB58-BP1** 3.6V

Panasonic



K

Eagle 940

3/P-30AARM 300mAh

**CTB59-BP1** 3.6V

Sanyo



A

Panasonic KX-TC1801, KX-TC1851, KX-TC1871, KX-TC1890, KX-TG2503AL, KX-TG2583AL replaces original batteries (P-F508PA, P-P510PA)

3/KR900AAEC 900mAh

◆ Denotes this battery is Nickel Metal Hydride replacement for original Nickel Cadmium battery. Where only the brand of phone the battery suits is mentioned, you need to consult us for the individual phone model type.

Please Note:  
All cordless phone battery cross-references are to be used as a guide only. Master Instruments has relied on information from telephone manufacturers, distributors and end users. Please be sure to check POLARITY, VOLTAGE & SIZE before installing. Master Instruments Pty Ltd will not be held responsible for damage caused due to the incorrect selection and installation of our range of cordless phone batteries. Many of the CTB batteries have the same connector but the polarity is in reverse, so please ensure polarity is correct.  
E.O.E. - All information contained herein is assumed to be accurate, however no responsibility is assumed by Master Instruments Pty Ltd for its use, nor for any infringements of patents or other rights of third parties which may result from its use. Please assist us in the addition, omission and correction of this where possible by contacting one of our sales representatives.

## Battery Connector Guide



**Be sure to check polarity, size and voltage before installing!**